



PRODUCT SPEC SHEET

SKU 217409

Model:VT-1879N-N

EAN:3800157682633

VT-1879 4.5W G45 PLASTIC BULB 6500K E27



IP20
STANDARD

02 YEAR
WARRANTY

- Modern LED SMD technology for better reliability and durability
- Replaces 40 watts old halogen lamp
- Lasts 20,000 Hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Inner Box Qty:	10
On/Off Cycles:	>20000
Model:	VT-1879N-N
Color Temperature:	6500K
CRI:	>80
Watts:	4.5
Lumens:	470
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	40
Unit Color:	White
Color for Web:	White
Body Type:	Thermoplastic
Dimension:	46x82mm
Base:	E27
Shape:	G45
PF:	>0.5

LISTING DETAILS

SKU:	217409
Model:	VT-1879N-N
EAN:	3800157682633
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.02
Unit CBM:	0.000225
Dimension:	46x82mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	7200
Length (Box) mm:	50
Width (Box) mm:	50
Height (Box) mm:	90

LED Chip Type:	SMD
Beam Angle:	180°
Energy Rating Label:	F (2021)
IP Rating:	IP20
Long Life:	20,000 Hours
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate