



PRODUCT SPEC SHEET

SKU 211931

Model:VT-247-N-N

EAN:3800170227392

VT-247 6W GU10 RIPPLE PLASTIC SPOTLIGHT 4000K 110'D



IP20
STANDARD

02 YEAR
WARRANTY

- Stable SMD technology for better reliability
- Lasts 20,000 Hours, longer life span than Standard halogen spotlights
- Replaces 60 watts old halogen lamp
- Easy to install, designed with GU10 base
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

TECHNICAL INFORMATION

Dimmable:	No
Inner Box Qty:	10
On/Off Cycles:	>20000
Model:	VT-247-N-N
Color Temperature:	4000K
CRI:	>80
Watts:	6
Lumens:	445
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	60
Unit Color:	White
Color for Web:	Day White
Body Type:	Plastic
Dimension:	50x55mm

LISTING DETAILS

SKU:	211931
Model:	VT-247-N-N
EAN:	3800170227392
Commodity Code:	8539521000

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000225
Dimension:	50x55mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	7200
Length (Box) mm:	50
Width (Box) mm:	50

Operation Temperature:	-20°C to +45°C
Base:	GU10
LED Chip Type:	SMD
Beam Angle:	110°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	20,000 Hours
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Height (Box) mm:80