




NOTES:

1. MATERIAL

- 1.1 HDMI CABLE: (7/0.1BC*1P+7/0.1BC+FAM)*4PCS+7/0.10BC*5C+7/0.10BC*1P+AL
+7/0.12BC+128/0.12ALM+BLACK PVC JACKET.

OD: $\varnothing 6.0 \pm 0.2$ mm

CABLE MARKING: E324703  AWM STYLE 20276 80°C 30V
HIGH SPEED HDMI® CABLE.

- 1.2 HDMI 19PIN TYPE A MALE: BLACK INSULATION, GOLD PLATED
CONTACTS 3u", GOLD PLATED SHELL G/F.

- 1.3 HDMI 19PIN TYPE A FEMALE: BLACK INSULATION, GOLD PLATED
CONTACTS 3u", GOLD PLATED SHELL G/F.

- 1.4 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
2.4 HI-POT: DC200V/0.01S.
2.5 HDTV-DVD TEST:1080P PASS.

3. PACKAGING: A PC/PE-BAG PACKAGING .


4. ALL MATERIALS ARE RoHS COMPLIANT.

PIN OUT

P1	P2
1	1 BLUE
3	3 WHITE
2	2 DRAIN
4	4 BLUE
6	6 WHITE
5	5 DRAIN
7	7 BLUE
9	9 WHITE
8	8 DRAIN
10	10 BLUE
12	12 WHITE
11	11 DRAIN
13	13 GREEN
14	14 PURPLE
15	15 YELLOW
16	16 ORANGE
17	17 RED
18	18 WHITE
19	19 BLUE
SHELL	DRAIN SHELL

P/N

ITEM NO.	L(mm)
AV21436	2000±50mm
AV21437	3000±70mm
AV21438	5000±70mm

LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1		SCALE: FREE		CUS. NAME: CPC				ENG: kevin			
ANGLE TOLERANCE: X° ±3° .X° ±1°		UNIT: mm						PRODUCT NO:		CUSTOMER NO: SEE THE P/N CHART	
		VERSION: 00				DRAWING NO:		PRODUCT DESCRIPTION: HDMI AM-90° AM/GOLD-PLATED		APPROVED: sunny	
		PAGE: 1/1									
3		4		5		6		7			

00	NEW ISSUE	2011-11-3
REV.	MODIFY DESCRIPTION	DATE