



Charge 'n' Go Power Bank 27000mAh 183W

PN: 32269

Description

Power to Keep You Going : The Verbatim Charge 'n' Go Power Bank, with its robust 27,000mAh capacity, is designed for the power-hungry devices you rely on. Whether you're charging a laptop, smartphone, or tablet, it ensures you stay connected throughout your busy day. Perfect for work, play, or travel, it offers enough power for multiple charges, so you can share with others or keep your devices running longer during outdoor adventures.

High Power PD 3.1 Fast Charging: Featuring advanced PD 3.1 charging technology, the Verbatim Charge 'n' Go Power Bank supports high power fast charging up to 140W via two USB-C ports. Along with a USB-A port equipped for QC 3.0 fast charging up to 18W, it can support charging up to 3 devices simultaneously.

Stay Informed: Equipped with a smart digital TFT display, the Verbatim Charge 'n' Go Power Bank keeps you informed about the remaining power. The lightning bolt icon on each port indicates the wattage during charging, letting you know if fast charging is active. The color-coded system shows whether the product is charging in (Green) or charging out (Orange).

Smart, Bi-directional Charging: With a bi-directional USB-C port, this power bank handles both charging in and out through a single port, simplifying your charging routine.

Trusted On-the-Go Energy: Your safety is our priority. The Charge 'n' Go Power Bank is designed with 5 essential protection systems—overcurrent, short circuit, overcharge, over-discharge, and over-temperature protection—ensuring a secure charging environment for all your devices.



Charge 'n' Go Power Bank 27000mAh 183W

PN: 32269

Product Specifications

- Battery Capacity: 27000mAh/ 99.9wh 3.7 V
- USB-C1/ C2 PD 3.0 Input: 5 V = 3 A, 9 V = 3 A, 12 V = 3 A, 15 V = 3 A, 20 V = 5 A (100W max.)
- USB-C1/C2 PD 3.1 Output (PPS supported): 5 - 11 V = 5 A, 5 V = 3 A, 9 V = 3 A, 12 V = 3 A, 15 V = 3 A, 20 V = 5 A, 28 V = 5 A (140W max.) Each
- USB-A Output: 5 V = 3 A, 9 V = 2 A, 12 V = 1.5 A (18W max.)
- Total Output: 183W max.
- Supports PD 3.1, QC 3.0 Apple 2.4A, BC1.2, DCP, AFC
- Safety Protection: Short circuit / Over current / Over temperature / Over charge voltage / Over discharge voltage protection
- Operating Temperature: 0 to +35 °C
- Operating Humidity: 50%-85%
- Storage Temperature: Under normal temperature conditions: -10 to +45 °C; charging and discharging every 3-4months

Languages

Front of pack: English

Back of pack: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese

Quick Installation Languages

English, German + Technical support text in English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, Korean, Japanese



PN	Capacity	Rated Capacity*	Colour	Pack Content:
32269	27000 mAh	~ 16200mAh	Grey	<ul style="list-style-type: none"> • Verbatim Charge 'n' Go Power Bank 27000mAh • USB-C® to USB-C® cable • Quick Start Guide

*Based on 5V-2.4A output.

Charge 'n' Go Power Bank 27000mAh 183W



Reorder No.	Description	Tariff Code	Barcode	EAN-128	EAN-14
32269	Charge 'n' Go Power Bank 27000mAh 183W Grey	85076000	023942322696	(02)00023942322696(37)0591843 (02)00023942322696(37)1091843	20023942322690 50023942322691

Reorder No.	32269
Product Dimensions L x W x H	156.5 x 52.8 x 49.7 mm
Product Weight	650 g
Units per Pack	1
Pack Dimensions L x W x H	222 x 80 x 57 mm
Pack Weight	754 g
Units per Inner Carton	5
Inner Carton Dimensions L x W x H	310 x 250 x 130 mm
Inner Carton Weight	4100 g
Units per Outer Carton	10
Outer Carton Dimensions L x W x H	330 x 265 x 270 mm
Outer Cartons Weight	8600 g
Outer Cartons per Layer	12
Layers per Pallet	5
Units per Pallet	600



Colour Display



Safety Protections



PD 3.1



Charge 3 Devices