

Flashlight XGT®

ML001G

40Vmax • 160 lm

Powerful LED flashlight with XGT® battery.

A handy tool for any kind of use where you need more light to see. 12 position pivoting flashlight head with positive stops from 0° - 170°. Runtime with 4,0 Ah XGT® battery is up to 55h.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Luminous flux	160 Lumen
Illuminance	3000 lx
LED wattage	4 x 0,5 W
Continuous Use XGT® 40V Max / 4.0 Ah	55 h
Product net weight	0,28 kg
Tool weight with battery	1,0 - 2,2 kg
Product Dimensions (L x W x H):	287 x 88 x 136 mm
Angle range vertical	170 °

User benefits

- Compact and lightweight design
- 12 position pivoting flashlight head
- Soft grip handle provides increased comfort on the job
- Battery protection circuit protects against overloading, over-discharging and over-heating

EAN 0088381730167

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing