



LG UHD AI 55UA73006 139.7 cm (55") 4K Ultra HD Smart TV Wi-Fi Black

Brand : LG

Product family: UHD AI

Product code:
55UA73006

Product name : 55UA73006

LG UHD AI 55UA73006. Display diagonal: 139.7 cm (55"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LED, Screen shape: Flat, LED backlighting type: Direct-LED. Smart TV. Native aspect ratio: 16:9. Digital signal format system: DVB-S, DVB-S2, DVB-T, DVB-T2. Wi-Fi, Ethernet LAN. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	139.7 cm (55")	Ethernet LAN (RJ-45) ports	1
HD type *	4K Ultra HD	USB 2.0 ports quantity *	2
Display technology *	LED	Digital audio optical out	1
LED backlight	✓	RF ports quantity	2
LED backlighting type	Direct-LED	Common interface (CI) *	✓
Screen shape *	Flat	Common interface Plus (CI+) *	✓
Native aspect ratio *	16:9	Common interface Plus (CI+) version	1.4
Native refresh rate	60 Hz	HDMI ports quantity *	3
Display resolution *	3840 x 2160 pixels	Consumer Electronics Control (CEC)	SimpLink
Display diagonal (metric)	139 cm		
TV tuner		Management features	
Tuner type *	Analog & digital	Voice guide	✓
Digital signal format system *	DVB-S, DVB-S2, DVB-T, DVB-T2	Electronic Programme Guide (EPG)	✓
Smart TV		Programming period	8 day(s)
Smart TV *	✓	On Screen Display (OSD)	✓
Internet TV *	✓	Number of OSD languages	38
Operating system installed *	WebOS	Picture-in-Picture	✗
Operating system version	25	Hotel mode	✗
Apple AirPlay 2 support	✓	Basic hotel mode	✓
Hybrid Broadcast Broadband TV (HbbTV)	✓	Works with Amazon Alexa	✗
Built-in Chromecast	✓	Works with the Google Assistant	✓
		Works with Samsung Bixby	✗
		Works with Apple Siri	✓
Audio		Power	
Number of speakers *	2	Power consumption (standby) *	0.5 W
RMS rated power *	20 W	Energy efficiency class (SDR) *	F
Audio output channels	2.0 channels	Energy efficiency class (HDR) *	G
Built-in subwoofer	✗		

Audio		Power	
Audio decoders	Dolby Digital	Energy consumption (SDR) per 1000 hours *	77 kWh
Sound modes	AI Sound Pro, Clear Voice Pro	Energy consumption (HDR) per 1000 hours *	105 kWh
Enhanced Audio Return Channel (eARC)	✔	AC input voltage	100-240 V
Network		AC input frequency	50/60 Hz
Wi-Fi *	✔	Energy saving mode	✔
Wi-Fi standards	Wi-Fi 5 (802.11ac)	Energy efficiency scale	A to G
Bluetooth *	✔	Brand-specific features	
Bluetooth version	5.1	LG technologies (AV/TV)	AI Sound Pro, AI Super Upscaling 4K, Bluetooth Surround Ready, LG Sound Sync, ThinQ™, WOW Orchestra
Ethernet LAN *	✔		
Bluetooth profiles	A2DP		
Web browser	✔		
Design		Weight & dimensions	
Product colour *	Black	Width (with stand)	1226 mm
VESA mounting *	✔	Depth (with stand)	292 mm
Panel mounting interface	300 x 300 mm	Height (with stand)	776 mm
Frameless design	✔	Weight (with stand)	10.4 kg
Introduction year	2025	Width (without stand)	1226 mm
Stand type	Legs stand	Depth (without stand)	58.9 mm
Performance		Height (without stand)	710 mm
High Dynamic Range (HDR) technology	Dynamic Tone Mapping, Filmmaker Mode, High Dynamic Range 10 (HDR10), Hybrid Log-Gamma (HLG)	Weight (without stand)	10.2 kg
		Stand width	122.3 cm
		Stand depth	29.2 cm
		Packaging data	
Game mode	✔	Package width	1385 mm
Teletext function	✔	Package depth	128 mm
Subtitles function	✔	Package height	830 mm
Video formats supported	AV1, HEVC/H.265, VP9	Package weight	14.9 kg
High Dynamic Range (HDR) supported *	✔	Packaging content	
Processor cores	4	Desktop stand	✔
Game features	Auto Low Latency Mode (ALLM), Game Optimizer, HGiG, Variable Refresh Rate (VRR)	Cables included	AC
		Remote control included	✔
Multi View	✔	Soundbar included	✘
Smartphone/tablet remote support	✔	Other features	
USB recording	✘	Digital Living Network Alliance (DLNA) certified	✔
DVD player	✘	Warranty period	2 year(s)
Ports & interfaces			
HDMI version	2.1		
Audio Return Channel (ARC)	✔		
PC in (D-Sub) *	✘		



8806096340301

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.