



Portable Radio

IPX4 splash resistant

Large LCD display

Bluetooth® 5.3

FM/DAB+ digital tuning



TAR5600

Splash-proof portable radio for home and garden

Great-sounding Bluetooth® clock radio with replaceable built-in battery and portable, splash-proof design. You get crystal-clear DAB+ or FM radio and stable streaming — plus there's a handy kitchen timer to keep your cooking on point!

FM/DAB+ Bluetooth® clock radio for inside or out

- Great sound. IPX4 splash-resistant design
- Dynamic Bass Boost for deeper bass
- Handy kitchen timer
- Large, easy to read display with adjustable brightness

Cordless, splash-proof and great in the kitchen!

- Easy wireless streaming via Bluetooth®
- FM/DAB+ digital tuner with 20 FM and 20 DAB+ presets
- Replaceable built-in battery and compact, portable build

Versatile functions. Responsible design.

- Dual alarms and Sleep Timer
- 3.5 mm audio-out for wired headphones
- GRS-certified recycled plastic. Responsible packaging
- Dimensions: (W x H x D) 222 x 147 x 96 mm

Highlights

Great sound. Splash resistant



From kitchen disco to brunch on the patio, this compact Bluetooth® portable radio will fill your room or outside area with rich sound. The splash-resistant design is great in the kitchen, the bathroom or even the garden — and you can use Dynamic Bass Boost to deepen the bass when it's time to dance!

Handy kitchen timer



If you like to listen while you cook, you can set the radio's kitchen timer to help keep track of your dishes. The large, clear LCD display counts down the hours, minutes and seconds while the big clock digits let you quickly see how much time is left.

Large LCD display



The clear LCD display with big clock digits makes it easy to see what time it is—or read the artist and song information from the DAB+ station that you're listening to. You can adjust the brightness to suit your room or dim the display at night.

Bluetooth® 5.3

This radio does more than just radio. Bluetooth® 5.3 connectivity lets you stream podcasts, playlists and more from your smart device to the radio, and you'll enjoy a stable connection indoors and out.

FM/DAB+ digital tuner

Music, news, drama, or sports? This DAB+/FM radio gives you the widest selection of stations and crystal-clear reception. Digital tuning makes your favourite stations super easy to find, and you can store 20 FM presets and 20 DAB+ presets for quick and easy listening.

Replaceable built-in battery

With a built-in battery that's easily replaceable when it reaches the end of its life, you can depend on this compact portable radio for years

to come! A built-in handle makes it easy to carry the radio, and you get approx. 10 hours play time from a full charge if volume is kept at 70 %. The battery is charged via USB-C.

Dual alarms and Sleep Timer

If you like falling asleep to the sound of the radio, you can use the Sleep Timer to control how long the radio plays for—and set two alarms to ensure that you wake up. Alarms can use an alarm tone or the radio, and the volume starts low before gradually increasing.

Audio out

Want to enjoy your favourite radio show while your partner watches TV? A 3.5 mm audio-out jack means you can plug your wired headphones into the radio and keep your sounds to yourself.

Responsible design



We're continually working to make our supply chain more sustainable and transparent. This clock radio is made with post-consumer recycled plastics, and our packaging uses FSC-certified recycled cardboard and soy-based ink.



digitalradio  DAB+ DAB FM certified

Specifications

Sound

Output power (RMS): 5 W
Sound System: Mono
Volume control: rotary (digital)
Output power (MAX): 10 W
Total harmonic distortion: <10%
Dynamic Bass Boost

Loudspeakers

Full-range driver diameter: 3"
Number of full-range drivers: 1

Connectivity

Bluetooth: Yes, support SBC and AAC streaming
Bluetooth version: 5.3
Bluetooth profiles: A2DP, AVRCP
Bluetooth range: Line of sight, 30 m or 100 ft
3.5 mm headphone jack
Audio in: No

Tuner/Reception/Transmission

Antenna: Telescopic
Auto digital tuning
Tuner bands: FM, DAB/DAB+
Station presets: 20 FM, 20 DAB+
DAB: info display, menu, smart scan
RDS: Yes.

Convenience

Backlight colour: white
Display type: LCD display
Waterproof: IPX4

Power

Battery Capacity: 3.65 V, 2600 mAh
Battery type: Li-ion polymer (replaceable)
Input: 5V, 1.5A
Standby power consumption: <0.8 W (clock display on)
Operating time on battery: 10 hour(s)
Power type: DC in (via USB-C)
Charging time: 3.5 hour(s)

Packaging dimensions

Height: 19.8 cm
Packaging type: Box
Type of shelf placement: Standing
Width: 27.7 cm
Depth: 14.8 cm
Number of products included: 1
Gross weight: 1.424 kg
Net weight: 0.964 kg
Tare weight: 0.46 kg

Product dimensions

Height: 14.7 cm
Width: 22.2 cm
Depth: 9.6 cm
Weight: 0.887 kg

Accessories

Included accessories: USB cable, Quick start guide, Warranty certificate

Alarm

Alarm source: DAB radio, FM radio, Buzzer
No. of alarms: 2
Sleep timer: 15/ 30/ 60/ 90/ 120 mins
Snooze (repeat alarm): 10/20/30/40/50/60 mins
Gentle Wake
Kitchen timer

Clock

Display: LCD
Type: Digital
Time format: 12 H, 24 H
Brightness control (Dim)

Sustainability

Plastic shell: contains 80% GRS-certified recycled post-consumer acrylonitrile butadiene styrene
TE-00132492

