



## Open-ear true wireless earbuds

### 2000 series

True wireless open earbuds

Ear-cuff style

Up to 28 hours play time

Bluetooth multipoint



TAQ2000BK

## Ear-cuff style. Open-ear fit.

Enjoy clear audio and all-day comfort with the true wireless open earbuds that you wear like an ear cuff. Each bud clips on lightly but securely, while the open-ear design lets you hear the world as well as what you're listening to.

### True wireless open earbuds. Ear-cuff style.

- Ear-cuff style open earbuds. Comfy all day
- Up to 28 hours play time. Slimline charging case
- Stable Bluetooth multipoint connectivity

### Responsible design

- Responsible design and packaging
- GRS-certified post-consumer recycled plastics
- Plastic-free packaging and soy-based ink
- IPX4 splash and sweat resistant

### Your stylish everyday companion

- Clear calls. They'll hear what you're saying
- Customizable on-ear controls
- Philips Headphones app. Personalize your earbuds

# Highlights

## Ear-cuff style open earbuds



These open earbuds clip on lightly but securely to your outer ear and a flexible joint lets you adjust the grip for maximum comfort. Precision air-conduction drivers direct sound into your ear canal without sealing it, so you'll hear what's going on in your immediate surroundings too.

## 28 hrs play time (7 + 21)



You get 7 hours play time from a full charge, and an extra 21 hours from the case. If you need a quick boost, pop the earbuds back in the case for 15 minutes to get an extra hour. It takes 2 hours to recharge the earbuds fully, and mono mode lets you use one earbud at a time while the other one charges.

## Bluetooth 5.4 multipoint



Advanced Bluetooth connectivity gives you a more stable connection for seamless streaming, and you can connect to two Bluetooth devices at the same time. Enjoy that playlist or listen uninterrupted to your favorite podcast without annoying dips in the sound.

## Responsible design



We're continually working to make our supply chain more sustainable and transparent. These earbuds are made with GRS-certified post-consumer recycled plastics, and our plastic-free packaging uses FSC-certified recycled cardboard and soy-based ink.

## Philips Headphones app

As well as customizing the on-ear controls, you can use our companion app to activate Dynamic Bass, get the latest firmware updates, manage connected devices, and even listen to in-app soundscapes. There are soundscapes that you can play together with binaural beats to aid focus, relaxation, or sleep. Or try the ambient and nature soundscapes.

## IPX4 splash/sweat resistant

With their featherlight design, comfortable fit, and an IPX4 rating, these true wireless open earbuds are ready for everyday use. Fully splash resistant, they won't mind a little sweat and you don't need to worry about getting caught in the rain.

## Clear calls

Your voice will come through clearly when you're on a call. A dedicated mic picks up the sound of your voice while a noise-reduction algorithm quietens some of the background noise from the world around you.

## On-ear controls

There are handy button controls on the earbuds for playback, volume, and calls. Prefer to use the left or right earbud? You can customize how these controls are set up via the Philips Headphones companion app.

# Specifications

## Sound

**Frequency range:** 100 - 20,000 Hz  
**Speaker diameter:** 12 mm  
**Impedance:** 16 Ohm  
**Maximum power input:** 20 mW  
**Sensitivity:** 113 dB (1K Hz, 1mW)  
**Driver type:** Dynamic

**Battery type(Charging case):** Lithium Polymer (built-in)  
**Battery type(Earbud):** Lithium Polymer (built-in)  
**Battery weight (Total):** 11.2 g  
**Battery capacity(Case):** 450 mAh  
**Battery capacity(Earbud):** 51 mAh

## Sustainability

**Plastic shell:** contains 65% GRS certified recycled post-consumer Acrylonitrile Butadiene Styrene TE-00132492

## Connectivity

**Bluetooth version:** 5.4  
**Bluetooth profiles:** HFP, A2DP, AVRCP  
**Maximum range:** Up to 10 m  
**Multipoint connection**  
**Supported codec:** SBC

## Packaging dimensions

**Height:** 9.80 cm  
**Packaging type:** Carton  
**Type of shelf placement:** Hanging  
**Width:** 9.65 cm  
**Depth:** 3.40 cm  
**Number of products included:** 1  
**EAN:** 48 95229 15916 7  
**Gross weight:** 0.091 kg  
**Nett weight:** 0.067 kg  
**Tare weight:** 0.024 kg

## Accessories

**Quick Start Guide**  
**Charging case**  
**Charging cable:** USB-C cable, 200 mm

## Design

**Color:** Black  
**Wearing style:** Ear-clip  
**Ear fitting:** Open-ear  
**In-ear fitting type:** Open fit

## Telecommunication

**Microphone for call:** 1 mic

## Convenience

**Water resistance:** IPX4  
**Philips Headphones app support**  
**Mono mode for TWS**  
**Firmware updates possible**  
**Type of controls:** Button

## Dimensions

**Charging case dimension(WxDxH):** 6.55 x 2.77 x 3.92 cm  
**Earbud dimension(WxDxH):** 2.60 x 2.70 x 1.95 cm  
**Total weight:** 0.048 kg

## UPC

**UPC:** 8 40063 20599 4

## Inner Carton

**Length:** 11.10 cm  
**Number of consumer packagings:** 3  
**Width:** 10.40 cm  
**Height:** 8.50 cm  
**Nett weight:** 0.20 kg  
**Gross weight:** 0.290 kg  
**Tare weight:** 0.09 kg  
**GTIN:** 2 48 95229 15916 1

## Voice assistant

**Voice assistant compatible:** Apple Siri, Google Assistant  
**Voice assistant activation:** Multi-Function touch  
**Voice assistant support**

## Power

**Number of batteries:** 3  
**Music play time:** 7 + 21 hour(s)  
**Charging time:** 2 hour(s)  
**Fast charging time:** 15 mins for 1 hour

