



2 Piece Combo Kit LXT®, **DLX2590TJ**

18V

Includes: DHP492 Combi Drill and DTW300 Impact Wrench



Models in kit



**Combi Drill LXT®
DHP492**



**Impact Wrench LXT®
DTW300**

Combi Drill LXT®

DHP492

18V

A powerful, brushless general-use impact drill for screwdriving and drilling

An efficient, brushless drill for screwdriving and drilling. A powerful max. torque of 141Nm. The main feature and benefits are: Redesigned speed change mechanism to avoid gear disengagement, Controller protection has been revised to enhance the protection for electronic components during variable speed control by the trigger.



LXT **BL**
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 550 / 2100 min ⁻¹
Max. fastening torque Hard/Soft	130 / 65 Nm
Max Torque	141 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 8250 / 31500 min ⁻¹
Max. Drilling Diameter in Masonry	16 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	50 mm
Drilling Capacity Wood (Self-feed bit)	76 mm
Drilling Capacity Flat bit	40 mm
Drilling Capacity Hole Saw	152 mm
Driving Shank	1/2"-20UNF "

User benefits

- Highly efficient and compact machine for professional use
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low
- Electronic overload protection protects the user and the device
- Keyless chuck for easy bit installation and removal
- Compact and lightweight for reduced operator fatigue
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makita.uk.com



Impact Wrench LXT®

DTW300

18V • 1/2" • 330 Nm • 0 – 3 200
min⁻¹

Extra-compact and efficient brushless impact wrench with three power settings

Powerful and extra-compact, 144 mm-long, 1/2" drive impact wrench. Small size and light weight make this tool easy to use, while offering a max. fastening torque of 330 Nm. Four power settings. A handy LED light.



LXT **BL**
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	100 / 160 / 210 / 330 Nm
No load speed	0 - 1000 / 1800 / 2600 / 3200 min ⁻¹
Impacts per Minute (IPM)	0 - 1800 / 2600 / 3400 / 4000 min ⁻¹
Drive Square	1/2 "
Tightening Capacity Standard Bolt	M10 - M20
Tightening Capacity High Tensile Bolt	M10 - M16
Sound Power Level (L _{WA})	108 dB(A)
Sound Pressure Level (L _{PA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	144 x 81 x 246 mm

User benefits

- Extremely compact thanks to a brushless motor
- Low power consumption thanks to brushless motor
- The narrow design of the handle ensures excellent handling
- Battery protection system automatically shuts off power when the battery level is low
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes

Link to product - www.makita.uk.com



Related products kit

Standard AC

821551-8

Makpac case (3)



Standard MA

BL1850B (2x)

Battery LXT® 5,0 Ah



Optional AC

122576-8

Stopper Pole



134874-8

Extension bar 1/2", 100 mm



122D10-2

Grip Assembly



134877-2

Universal Joint 84 mm



821550-0

Makpac case (2)



835L10-8

Makpac Type 2 Inner tray (2)



821550-0

Makpac case (2)



837670-0

MakPac (2) Inlay



837916-4

MakPac (2) Inlay



B-40185

Impact Socket 1/2" 21 X 38 mm



B-40222

Impact Socket 1/2" 27 X 42 mm



B-40238

Impact Socket 1/2" 30 X 44 mm



E-12354

Impact deep socket set, 3 pcs



Other - DHP492

User manual

Parts drawing

Other - DTW300

User manual

Parts drawing