

Heat Gun XGT®

HG001G

40VMax, up to 600°C, 200 L/min

Model HG001G is a heat gun powered by a 40VMax XGT Li-ion battery

The machine achieves maximum temperature equivalent to our AC models. It offers excellent efficiency in demanding tasks requiring high temperature and air volume which can be adjusted. Features: LCD display. Nozzle quick release. Compatibility with the existing nozzles



Technical specifications

Nominal Battery Voltage	40 V
Continuous Use XGT® 40V Max / 4.0 Ah	14 min
Tool power source	1641
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Maximum Flow Rate	120 / 150 / 180 / 200 L/min
Tool weight with battery	1,5 - 2,7 kg
Product net weight	0,8 kg
Product Dimensions (L x W x H):	191 x 86 x 272 mm
Max. Temperature	600 °C
Variable Temperature	✓

User benefits

- Single LED job light illuminates the work area

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing