

# Pruning Shear LXT®

## DUP181

18V

Model DUP181 is cordless pruning shears powered by an 18V LXT Li-Ion battery.

Max cutting diameter  $\varnothing$ 30mm. Two control buttons, the main power button and blade angle adjustment button are located side by side on the rear of the grip for easy operation. External oil port. LED indicators



### Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
Sound Pressure Level ( $L_{pA}$ )	$\leq 70$ dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,1 - 2,1 kg
Product Dimensions (L x W x H):	300 x 75 x 113 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Product net weight	0,76 kg
Vibration Level, No load	$\leq 2,5$ m/s <sup>2</sup>
Vibration Uncertainty (K Factor), No load	1,5 m/s <sup>2</sup>
Max Cutting Capacity	30 mm
Electronic brake	✓

### User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

[Link to product - www.makita.com](http://www.makita.com)



# Related products

## ■ Other

User manual

Parts drawing