



Features

- 1200 W POWER
- 260 ML EASY-TO-FILL WATER TANK
- FAST HEAT-UP TIME - 45-50 SECONDS
- 12-15 MINUTES OF CONTINUOUS STEAM
- COMPACT FOR EASY STORAGE
- 1.9 M POWER CORD
- INCLUDES 2 IN 1 FABRIC AND LINT BRUSH AND MEASURING JUG



www.beldray.com

Shipping Details / Product Details

Carton Qty: 6

Container Qty:

20 Ft: 3522

40 Ft: 7260

40 HQ: 8640

Carton Details: 40.50l x 32.00w x 36.50h cm

CBM: 0.05

Carton Weight Net: 7.13 kg

Carton Weight Gross: 7.57 kg

Port: NINGBO

Product Code: BEL0815

Packaging Type: Closed Colour Box

Box Size: 30.50l x 13.00w x 17.00h cm

Product Size: 13.00l x 11.00w x 28.00h cm

MOQ: 2000

Barcode: 5054061102413

TUC: 05054061102420

Commodity Code: 8516 7970 90

Duty: 2.70%

Important:

The unit prices quoted on this document includes certification of the product to ensure compliance with mandatory UK and European legislation.

Please note: Any optional non-mandatory testing is not included in the quoted price. Any optional testing requirements, and subsequent cost revisions, must be agreed prior to an order being placed. Any optional testing requested after the order is placed will not be funded by Ultimate Products.

UP Global Sourcing T/A Ultimate Products

Unless otherwise agreed and confirmed in writing, this offer is subject to the standard terms and conditions of Ultimate Products.

These are available at www.upgs.com/terms.

Retail price provided for information only: retailers are free to set their own retail prices.