



Downflow Heater
2KW Downflow Heater with Runback Timer

DESCRIPTION

2KW adjustable downflow heater with run back timer utilising fire retardant polycarbonate and ABS construction. Pull cord provided for simple control and dip switch controls to adjust power output between 1kW and 2kW to suit a range of room size and to adjust the run back timer

- FEATURES**
- Up to 2kw heat output for fast heating
 - Mains indicator light & pull cord on/off switch
 - Thermal cut out
 - Internal load switch 1kW / 2kW: allows output adjustment to suit room size
 - Up to 35 minute runback timer - adjustable upon installation
 - Select desired mode of operation using the dip switches

GENERAL INFORMATION			
Colour / Finish	White	Application	Internal
Product Warranty	1 Year	Net Weight	1.6 kg
TECHNICAL INFORMATION			
Nominal Voltage	240 V	Construction Materials Line 1	Fire-retardant ABS + PC
PRODUCT INFORMATION			
Wattage Combined	2,000W	Luminaire Lumens Combined	-
IP Rating	IP21		





PACKAGING	
Packaging Type	Colour Box
Individual unit gross weight	1,488 g
Pallet Layer Qty	30
Pallet Layers	5
Pallet Qty	150
MOM / OPQ	1 / 6

