



PCIe 8xRS232 DB25 1MBaud

PX-275/ PX-279: Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable	8 x RS232 DB25 connector (25 Pin Male) 256 RX FIFO + 256 TX FIFO EIA - RS232 Standard 8 port cable (78 WAY D -> 8 x 9 Pin or 8 x 25 Pin)
Port Settings 115,200 baud	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	115,200 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 RTS/CTS DSR/DTR XON/XOFF Point to Point
Interface 	OS Compatibility BUS	Windows Server 2008 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit Editions Windows Server 2003 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions Microsoft Windows 2000 PCI Express x1, x4, x8 & x16 lane slots :
Approvals 	Other Approvals Microsoft Approvals	WEEE RoHS METL EMC: CE Microsoft Certified Gold Partner Windows Server 2008 32 bit & 64 bit editions Windows Vista 32 bit & 64 bit editions Windows Server 2003 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions
General	PCB Layers Power Consumption Weight Size	4 490mA @ 3.3V, 210mA @ 12V 0.0 Kg 0x0x0 mm
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities PCIe 8xRS232 DB25 1MBaud / PCIe 8xRS232 (8x9 pin cable) 8 port cable (78 WAY D -> 8 x 9 Pin or 8 x 25 Pin)
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com