



PRODUCT SPEC SHEET

SKU 806-27

Model:VT-8623

EAN:3800170254862

VT-8623 8W/16W/20W LED DOME LIGHT (EMERGENCY) 3IN1 RD IP54



- Uses High Quality Power Driver and LED Chip
- Built-in switch for CCT and Wattage changing
- Powerful LED light source with lumen efficiency of 120 LM/W
- Hinged LED gear tray for easy installation
- Emergency backup for more than 3 Hours
- IP54 Ingress protection
- IK protection IK08
- Withstands weather, dust and vandalism
- Applications - Passage, Exterior walls, Airport, Malls, Security Lighting etc
- Maintained operation

TECHNICAL INFORMATION

Dimmable:	No
Emergency Standby	1.2
Watts:	
Emergency Operation	>3 Hours
Time:	
Battery Charging Current:	250mA
Battery Discharge Current:	410mA
Model:	VT-8623
Color Temperature:	3IN1
Battery Type:	LiFePO4, 3.2V 2Ah Battery
CRI:	>80

LISTING DETAILS

SKU:	806-27
Model:	VT-8623
EAN:	3800170254862
Commodity Code:	94051140

PACKAGING

Gross Weight (Kgs):	1.35
Unit CBM:	0.013566
Dimension:	320x100mm

MASTER BOX PACKAGING

Box Qty:	10
-----------------	----

Watts:	20
Lumens:	2600
Input Power:	AC:200-240V, 50Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	PC
Dimension:	320x100mm
Shape:	Round
PF:	>0.9
LED Chip Type:	SMD
Beam Angle:	110°
Energy Rating Label:	E (2021)
IP Rating:	IP54
IK Rating:	IK08
Long Life:	30,000 Hours
lumens per watt:	120

Qty Per Pallet:

Length (Box) mm:	330
Width (Box) mm:	110
Height (Box) mm:	330