



PRODUCT SPEC SHEET

SKU 218174

Model:VT-885-N-N

EAN:3800157676908

VT-885 5W SPOTLIGHT FIRERATED FITTING SAMSUNG CHIP 4000K NICKLE



IP65
STANDARD

05
YEAR
WARRANTY



- Fire-rated to resistance of 30,60,90 Mins
- Efficient replacement for traditional downlight fittings
- Swift connection - Quick Connector included
- Fitted with high efficiency Samsung LED Chips that offer up to 80% in energy savings
- Robust Iron build
- IP65 Protected for Outdoor use
- Spring Clips for safer installation and easy Maintenance
- Suitable for living rooms, bedrooms, utilities, corridors etc

TECHNICAL INFORMATION

Dimmable:	Yes
On/Off Cycles:	>20000
Cutting Size:	57mm
Model:	VT-885-N-N
Color Temperature:	4000K
CRI:	>80
Watts:	5
Lumens:	500
Input Power:	AC:220-240V, 50Hz
Unit Color:	Satin Nickle
Color for Web:	Day White
Body Type:	Iron
Dimension:	81.5x57mm
Shape:	Round

LISTING DETAILS

SKU:	218174
Model:	VT-885-N-N
EAN:	3800157676908
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.23
Unit CBM:	0.001089
Dimension:	81.5x57mm

MASTER BOX PACKAGING

Box Qty:	60
Qty Per Pallet:	
Length (Box) mm:	110

PF: >0.9

LED Chip Type: SMD-Samsung Chip

Beam Angle: 70°

IP Rating: IP65

Long Life: 30,000 Hours

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

Width (Box) mm: 90

Height (Box) mm: 110