



ROHS COMPLIANT




WIRING:

COLOR	US PLUG	JACK1	JACK2	JACK3	JACK4
WHITE/DRANGE (白橙)	1			4	
DRANGE (橙)	2			3	
WHITE/GREEN(白绿)	3		4		
BLUE(蓝)	4	3			
WHITE/BLUE(白蓝)	5	4			
GREEN(绿)	6		3		
WHITE/BROWN(白粉)	7			4	
BROWN(粉)	8			3	



ASSEMBLY:



⑨	PCB	FR-4	1.6mm	1	ZPFR06X5
⑧	LABEL	—	55*20.5mm	1	KLXXXX435
⑦	012N JACK	PBT	6P2C GRAY	4	JP012NX62XXXXXX-8H
⑥	BOTTOM HOUSING	ABS	GRAY	1	AHP-J-48DXXXXXX
⑤	UPPER HOUSING	ABS	GRAY	1	AHP-J-48UXXXXXX
④	MOLDING(1)	PVC	GRAY	1	SR
③	MOLDING(2)	PVC	GRAY	1	SR
②	CABLE	—	CAT.5e 24AWG GRAY	1	TC8C24XXXXXCS101
①	PLUG	PC	US PLUG 8P8C	1	PG68X2000XY0-1-H3 PG68X100BX00
ND	NAME	MATERIAL	SPECIFICATION	QTY	REMARK
APPD.		P/N	TLXX8C24XXXXSE94-G		
CHKD.		FILE	TLXX8C24XXXXSE94.DWG		
DR.		TITLE	TL		

TUK Ltd
Product Code: ADQ64

SCALE	/	SIZE	A4
UNIT	MM	REV.	A2

REV.	1	2	3	4	5	6	7
DESCRIPTION							
ENG.							
APPROVAL							