



# SS80S & SS80CS

- 80mm wide solid hardened steel lock body
- 6-pin cylinder
- Anti-drill protection
- Electrophoretic anti-corrosion finish
- Weather resistant protective body sleeve with keyhole dust cover
- 16mm diameter hardened boron steel shackle
- CEN grade 6 accredited
- LPCB SR3 accredited
- Secured by Design accredited
- Sold Secure approved
- Key blank: KB P6
- Squire security rating: Very High
- 10 year manufacturer guarantee



Product Name	Body Width	Body Height	Body Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance	Approx. Height	Approx. Weight
SS80S	80 mm	90 mm	40 mm	16 mm	32 mm	32 mm	120 mm	1.98 kg
SS80CS	80 mm	110 mm	40 mm	16 mm	25 mm	23.5 mm	120 mm	2.18 kg