



SS65S & SS65CS

- 65mm wide solid hardened steel lock body
- 6-pin cylinder
- Anti-drill protection
- Electrophoretic anti-corrosion finish
- Weather resistant protective body sleeve with keyhole dust cover
- 12.7mm diameter hardened boron steel shackle
- SS65CS CEN grade 6 accredited
- SS65S CEN grade 5 accredited
- Secured by Design accredited
- Sold Secure approved
- Key blank: KB P6
- Squire security rating: Very High
- 10 year manufacturer guarantee



Product Name	Body Width	Body Height	Body Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance	Approx. Height	Approx. Weight
SS65S	65 mm	75 mm	31.8 mm	12.7 mm	29 mm	29.5 mm	112 mm	1.03 kg
SS65S/2.5	65 mm	75 mm	31.8 mm	12.7 mm	65 mm	29.5 mm	148 mm	1.09 kg
SS65CS	65 mm	90 mm	31.8 mm	12.7 mm	19 mm	19 mm	100 mm	1.07 kg