



# CP40S

- 40mm die cast alloy lock body
- Dual compound weather resistant cover with push button opening
- Double locking
- Rustproof stainless steel shackle
- Available with standard shackle & long shackle
- Fully recodable 4-wheel dial with 10,000 possible combinations
- Keyless protection - no extra key to carry around or lose
- Designed for marine applications
- Compact & sturdy design
- Salt spray tested for over 200 hours
- Suitable for outdoor home & leisure use
- Squire security rating: Medium
- 10 year manufacturer guarantee



CP40S



CP40S



CP40S/2.5

Product Name	Body Width	Body Height	Body Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance	Approx. Height	Approx. Weight
CP40S	40 mm	45 mm	22 mm	6 mm	20 mm	17 mm	71 mm	0.09 kg
CP40S/2.5	40 mm	45 mm	22 mm	6 mm	63 mm	17 mm	114 mm	0.11 kg