



# CP50/ATLO

- 50mm die cast steel padlock body
- Robust TPE body cover for all terrain use
- Bright orange for high visibility applications & visible deterrent
- Ergonomic rubber sides for better grip in wet conditions
- Fully recodable 4-wheel dial with weather protective cover
- Keyless protection - no extra key to carry around or lose
- 10,000 possible combinations
- Angled push button for one handed operation & easier opening
- Hardened steel shackle with anti-corrosion finish
- Available with standard shackle & long shackle
- Salt spray tested for 312 hours offering outstanding performance designed to be used in the harshest all terrain environments
- Squire security rating: Medium
- 10 year manufacturer guarantee



CP50/ATLO



CP50/ATLO



CP50/ATLO/2.5

Product Name	Body Width	Body Height	Body Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance	Approx. Height	Approx. Weight
CP50/ATLO	50 mm	60 mm	36 mm	8 mm	23 mm	22 mm	94 mm	0.22 kg
CP50/ATLO/2.5	50 mm	60 mm	36 mm	8 mm	63 mm	22 mm	132 mm	0.24 kg