




1/4" MONO JACK SOCKET



Part No: **CL1166U** - 1/4" Mono Jack Socket S2/BNB/PC-C Unassembled

Jack Socket Specification

- Withstand voltage: 2000V DC minimum.
- Maximum current: 5 amps.
- Temperature rating: -10°C to +70°C.
- Life: Minimum 10,000+ operations.
- Nominal contact resistance: < 50mΩ.

