

Radio CXT® / LXT®

DMR301

12V max – 18V

High-quality radio for work or spare time with bluetooth

High quality workplace radio with IP64 protection rating. The radio operates on 12V max - 18V Li-ion batteries or mains power. Bluetooth connects directly to your music player. The radio has AUX and USB connectivity, and the ability to charge the battery. The radio supports listening to DAB / DAB + broadcasts. Bottle opener on the back cover of the radio.



Technical specifications

Nominal Battery Voltage	12 / 14,4 / 18 V
CXT Battery	✓
Voltage LXT	✓
Frequency Range AM	522 - 1710 kHz
Frequency Range FM	87,5 - 108 MHz
Frequency Range DAB+	174,928 - 239,200 MHz
Continuous Use 18V / 2.0 Ah Battery	8,2 h
Continuous Use 18V / 4.0 Ah Battery	16 h
Continuous Use 18V / 5.0 Ah Battery	20,5 h
Continuous Use 18V / 6.0 Ah Battery	24,5 h
International Protection Class (IP)	IP64
Tool weight with battery	5,9 - 6,6 kg
Product Dimensions (L x W x H):	268 x 185 x 305 mm
Continuous Use 14.4V / 3.0 Ah Battery	9 h
Continuous Use 18V / 3.0 Ah Battery	11 h
Bluetooth	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-)	Li-ion

User benefits

- AUX-IN jack allows for connection to personal audio players
- USB connector for charging your phone
- AC adapter supplied as standard
- Equipped with Bluetooth to wirelessly connect your mobile device to play music
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381899550

Link to product - www.makita.com



Related products

■ **Optional AC**

TC00000203

AC Adapter for DMR301 Jobsite



■ **Other**

[User manual](#)

[Parts drawing](#)