

WorkForce WF-110W

DATASHEET / BROCHURE



With the WF-110W, you can print anywhere with Epson's smallest and lightest wireless A4 inkjet printer that can be charged on the go via USB. This inkjet printer features an integrated battery, an LCD screen, Wi-Fi and Wi-Fi Direct connectivity.

For professionals needing to print on the go, Epson's A4 portable printer provides a high-quality solution. Small and light, this inkjet printer features an integrated battery, an LCD screen, Wi-Fi and Wi-Fi Direct connectivity, and compatibility with Epson iPrint*. It's great for printing invoices, contracts and more without worrying about wires.

Portable printing

The WF-110W is Epson's smallest and lightest wireless A4 inkjet printer. It measures just 309x154x61mm and weighs 1.6kg.

Print without a power cable

An in-built battery gives you the power to print 50 pages, which can be topped up simply by recharging it via USB. For even more flexibility, an optional external battery can give you the power to print up to 410 pages*.

Convenient

Print wirelessly with compatible solutions such as Google Cloud Print and Epson Connect. Use Epson iPrint* app for wireless printing from smartphones and tablets. It can even receive files to print from almost anywhere in the world via Epson Email Print*.

High-quality prints

The quality of this printer is reflected in the quality of the printouts. In fact, it is the only portable printer that uses pigment inks for all colours for durable, smudge-free results.

Efficient

The WF-110W delivers an ISO print speed of 7ppm in black and 4ppm in colour* and has an ink yield of up to 250 pages in black and 200 in colour*. With a 3.7cm LCD screen, it's easy to set-up a Wi-Fi connection without the need for a PC, and to check ink supply levels.

KEY FEATURES

- **Compact and lightweight for printing on the go**
High-quality printer that delivers an ISO print speed of 7ppm in black and 4ppm in colour* and has an ink yield of up to 250 pages in black and 200 in colour*.
- **Rechargeable battery**
With the power to print 50 pages, which can be recharged via any USB port or recharge with the bundled AC adaptor. For even more flexibility, an optional external battery can give you the power to print up to 410 pages*.
- **Wireless connectivity lets you print from anywhere**
Print easily from your smartphone or tablet using compatible solutions such as Epson iPrint app*.
- **Quality, durable, smudge-free prints**
It is the only portable printer that uses pigment inks for all colours for high-quality results.
- **User-friendly**
Hassle-free with simple set-up
- **Legal Statement**
Complies with The UK Product Security and Telecommunications Infrastructure (Product Security) requirements. Epson will provide security updates for 7 years from purchase



EPSON®

PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	1.5 pl, With Variable-Sized Droplet Technology
Ink Technology	Pigment ink
Nozzle Configuration	180 Nozzles Black, 59 Nozzles per Color
Category	Home
All-in-One Functions	Print

PRINT

Printing Speed ISO/IEC 24734	7 pages/min Monochrome, 4 pages/min Colour
Printing Speed ISO/IEC 24734	4 pages/min monochrome, 2 pages/min colour (battery operated)
Maximum Printing Speed	14 pages/min Monochrome (plain paper 75 g/m ²), 11 pages/min Colour (plain paper 75 g/m ²)
Printing Resolution	5,760 x 1,440 DPI

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

PAPER / MEDIA HANDLING

Paper Formats	A4 (21.0x29.7 cm), A5 (14.8x21.0 cm), A6 (10.5x14.8 cm), B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter Legal, 10 x 15 cm, 13 x 18 cm
Duplex	No
Paper Tray Capacity	20 Sheets Standard, 20 Sheets Maximum, 5 Photo Sheets
Number of paper trays	1
Compatible Paper Weight	64 - 300g/m ² Paper compatibility may vary by printer. Third party media may not be compatible. See printer's online User's Guide for suitable Epson paper and note that 300gsm, where applicable, is based on Epson Ultra Glossy Photo Paper

CONNECTIVITY

Interfaces	USB 2.0 Micro-B, Wireless LAN IEEE 802.11b/g/n, Wi-Fi Direct
------------	--

GENERAL

Energy Use	1.3 Watt (sleep mode), 11 Watt (Printing), 4 Watt (Ready), 0.3 Watt (Power off), TEC 0.18 kWh/week
Product dimensions	309 x 159 x 61 mm (Width x Depth x Height)
Product weight	1.6 kg
Noise Level	45 dB (A) according to ISO 9296
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10 (32/64 bit), Windows 7 (32/64 bit), Windows 8 (32/64 bit), Windows 8.1 (32/64 bit), Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Vista (32/64 bit), Windows XP SP3 or later (32-bit), Windows Server 2003 R2, Windows Server 2003 SP2 or later, XP Professional x64 Edition SP2

ADDITIONAL FEATURES

Panel	Type: Color, Diagonal:3.7 cm
-------	------------------------------

OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	C11CH25401DA
EAN code	8715946670829
Country of Origin	Philippines

For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.
Last extracted: 2026-01-16

WorkForce WF-110W

WHAT'S IN THE BOX

- 2x Maintenance box
- AC adapter
- Ink cartridges (1 black, 1 three-colour cartridge)
- Main unit
- Micro-USB cable

INK CARTRIDGE COMPATIBILITY



INK YIELD DATA



Globe 267

● 250 pages*

● 200 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. see www.epson.co.uk/for-home/ecotank

EPSON®