

# EcoTank ET-2811



## DATASHEET / BROCHURE



Perfect for anyone looking for low-cost-printing, this A4 inkjet printer has refillable ink tanks and up to 3 years' worth of ink included in the box\*. Additional benefits include mobile printing, Wi-Fi, copy and scan.

Save up to 95% on printing costs\* with Epson's cartridge-free EcoTank printers. Supplied with high yield ink bottles, the integrated ink tanks are easy to fill thanks to the specially engineered ink bottles. With no cartridges to replace, and flexible connectivity features, this is the perfect printer for anyone looking for high-quality prints at an incredibly low cost per page.

### Say goodbye to cartridges

EcoTank provides hassle-free home printing - the ultra-high capacity ink tanks allow mess-free refills and the key-lock bottles are designed so only the correct colour can be inserted. The front ink level display means it's easy to see when it's finally due for a refill.

### Keep on saving

This economical printer saves you up to 95% on printing costs\* and comes with up to 3 years' worth of ink included in the box\*. One set of ink bottles delivers up to 4,500 pages in black and white and 7,500 in colour\*.

### Epson Smart Panel app

This app enables you to control your printer from your smart device\*. You can print, copy and scan documents and photos, set up, monitor and troubleshoot your printer, all from your phone or tablet.

### Packed with features

Featuring a 100-sheet rear paper tray, borderless photo printing (up to 10x15cm) and print speeds of up to 10 pages per minute\*, you can speed through a variety of tasks with ease.

### Modern flexibility

Featuring a compact design and Wi-Fi and Wi-Fi Direct connectivity, you can easily integrate this printer with your existing home set-up and print from mobiles, tablets and laptops\*.

### Heat-Free Technology

With Micro Piezo Heat-Free Technology you can enjoy reduced energy consumption and less need for replacement parts. The printhead also comes pre-installed so setting up your printer is hassle-free.

## KEY FEATURES

- **Stress-free, convenient printing with up to 3 years' worth of ink included in the box\*.**  
Save up to 95% on printing costs\* with refillable ink tanks
- **A4 multifunction printer**  
High quality print, copy and scan in one machine
- **Wireless connectivity lets you print from anywhere**  
Use the Epson Smart Panel app to set up, monitor, print and more from your mobile
- **One set of inks prints up to 4,500 pages in black and 7,500 pages in colour\***  
Just add paper for low intervention printing!
- **Number 1 ink tank printer brand worldwide\***  
Over 100 million EcoTank printers sold worldwide\*
- **Simple hassle-free ink tank system lets you refill from bottles**  
Plus the EcoTank key-lock bottle system ensures it's mess-free too
- **Legal Statement**  
Complies with The UK Product Security and Telecommunications Infrastructure (Product Security) requirements. Epson will provide security updates for 7 years from purchase

## PRODUCT SPECIFICATIONS

### TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Ink Technology	Dye Ink
Printing Resolution	5,760 x 1,440 DPI
Nozzle Configuration	180 Nozzles Black, 59 Nozzles per Color
Category	Home
All-in-One Functions	Print, Scan, Copy

### PRINT

Number of colours	4 colour
Printing Speed ISO/IEC 24734	10 pages/min Monochrome, 5 pages/min Colour, 69 Seconds per 10 x 15 cm photo
Maximum Printing Speed	33 pages/min Monochrome (plain paper 75 g/m <sup>2</sup> ), 15 pages/min Colour (plain paper 75 g/m <sup>2</sup> ), 27 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)
Colours	Black [Dye], Cyan [Dye], Yellow [Dye], Magenta [Dye]
Colours Capacity	Black [65ml], Cyan [65ml], Yellow [65ml], Magenta [65ml]
First Page Out	Monochrome 10 Seconds, Colour 16 Seconds

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

### SCAN

Optical Resolution	1,200 DPI x 2,400 DPI (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

### PAPER / MEDIA HANDLING

Number of paper trays	1
Paper Formats	A5 (14.8x21.0 cm), A4 (21.0x29.7 cm), A6 (10.5x14.8 cm), B5, B6, C6 (Envelope), DL (Envelope), No. 10 (Envelope), 9 x 13 cm, 10 x 15 cm, 13 x 20 cm
Duplex	Manual
Paper Tray Capacity	100 Sheets Standard
Media Handling	Borderless Print (up to 10 x 15cm)

### GENERAL

Energy Use	12 Watt (standalone copying, ISO/IEC 24712 pattern), 0.7 Watt (sleep mode), 4.5 Watt (Ready), 0.2 Watt (Power off), TEC 0.15 kWh/week
Product dimensions	375 x 347 x 179 mm (Width x Depth x Height)
Product weight	3.9 kg
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10 (32/64 bit), Windows 11, Windows 7 (32/64 bit), Windows 8 (32/64 bit), Windows 8.1 (32/64 bit), Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Vista (32/64 bit), Windows XP Professional x64 Edition SP2 or later, Windows XP SP3 or later (32-bit), Windows Server 2003 R2, Windows Server 2003 SP2 or later
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES), WPA2 PSK (AES), WPA3-SAE(AES)
Mobile and Cloud printing services	Epson Smart Panel App, Epson Connect (Email Print, Remote Print Driver)
Colour	Black

### OTHER

Warranty	12 months Carry in, 30,000 pages Optional warranty extension available
----------	---

## LOGISTICS INFORMATION

SKU	C11CJ67402
EAN code	8715946684093
Country of Origin	Philippines

For more information please contact:

Home users: 0343 90 37766  
Business users\*: 0871 42 37766  
Republic of Ireland: 01 436 7742  
Or visit us at <https://www.epson.co.uk/contactus>  
\* 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.  
Product information is subject to change without prior notice.  
Last extracted: 2023-01-26

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

## EcoTank ET-2811

### WHAT'S IN THE BOX

- 4 x 65ml individual ink bottles (Bk, C,Y,M)
- Main unit
- Power cable
- Setup guide
- Warranty document

### INK BOTTLE COMPATIBILITY



### INK BOTTLE YIELD DATA

		
Included	3,600 pages*	6,500 pages*
Replacement	4,500 pages*	7,500 pages*

\* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. See [www.epson.co.uk/ecotankfootnotes](http://www.epson.co.uk/ecotankfootnotes) for more details

**EPSON**®