

Expression Photo XP-8700



The XP-8700 is an affordable, compact printer that can cater for both everyday printing and producing, superior, glossy photographs. It includes mobile printing, a large touchscreen and dual paper trays.

The Expression Photo XP-8700 is great if you're looking for an A4 printer that can cater for both everyday printing and producing superior, glossy photographs. Making everyday tasks easy, it includes mobile printing, a large touchscreen and dual paper trays.

Compact multifunction printer

Show off your photos to their very best with this A4 multifunction printer, that's designed to complement your home with its compact and stylish design.

User-friendly and versatile

Access photos directly via the memory card slot using the large 10.9cm touchscreen. It's easy to switch between tasks with the two front-loading paper trays (A4 and photo-sized) and a rear speciality media feed for thicker media. You can print onto suitable CDs and DVDs, and it also benefits from a motorised output tray, auto power on and A4 double-sided printing.

Flexible wireless solutions

Print, scan and more, directly from your phone or tablet using the Epson Smart Panel app*. Plus, with the Epson Creative Print app, you can use your photos to create and print photo books, greeting cards, collages and more.

Claria Photo HD Inks

Print professional, glossy photos with Claria Photo HD Inks. Photography enthusiasts and semi-professionals will appreciate the quality produced by its 6-colour, individual inks. Designed with longevity in mind, photos will last up to 300 years in a photo album*.



KEY FEATURES

- **Compact and versatile A4 multifunction printer with easy-to-use touchscreen**
High-quality print, copy and scan in one machine
- **Wireless connectivity lets you print from anywhere**
Use the Epson Smart Panel app to set up, monitor, print and more from your mobile
- **Produce superior, long-lasting, glossy photos**
With Epson Genuine 6-colour Claria Photo HD individual inks
- **Money and paper saving double-sided printing**
Automatically print on both sides to reduce paper usage and save money
- **User-friendly and versatile paper trays**
Front-loading paper trays for A4 paper and photo sized. Plus rear speciality media feed for thicker card and a motorised output tray.
- **Legal Statement**
Complies with The UK Product Security and Telecommunications Infrastructure (Product Security) requirements. Epson will provide security updates for 7 years from purchase



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	1.5 pl, With Variable-Sized Droplet Technology
Ink Technology	Claria™ Photo HD Ink
Printing Resolution	5,760 x 1,440 DPI

PRINT

Printing Speed ISO/IEC 24734	9.5 pages/min Monochrome, 9 pages/min Colour
Maximum Printing Speed	10 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper), 32 pages/min Colour (plain paper 75 g/m ²), 32 pages/min Monochrome (plain paper 75 g/m ²)
Colours	Black, Cyan, Light Cyan, Yellow, Magenta, Light Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Optical Resolution	1,200 DPI x 4,800 DPI (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

PAPER / MEDIA HANDLING

Number of paper trays	2
Paper Formats	Legal, Letter, 16:9, 13 x 18 cm, 10 x 15 cm, No. 10 (Envelope), DL (Envelope), C6 (Envelope), B5, A6 (10.5x14.8 cm), A5 (14.8x21.0 cm), A4 (21.0x29.7 cm), 9 x 13 cm, 13 x 20 cm, 20 x 25 cm, 100 x 148 mm
Duplex	Yes (A4, plain paper)
Print Margin	0 mm top, 0 mm right, 0 mm bottom, 0 mm left (Wherever margin is defined. Otherwise 3mm top, left, right, bottom.)
Paper Tray Capacity	100 Sheets Standard, 20 Photo Sheets
Media Handling	Automatic duplex (A4, plain paper), Borderless Print, CD/DVD print, Rear specialty media feed, Thick Media Support

GENERAL

Energy Use	7.2 Watt (Ready), 0.2 Watt (Power off), 20 Watt (standalone copying, ISO/IEC 24712 pattern), 0.7 Watt (sleep mode)
Product dimensions	349 x 340 x 142 mm (Width x Depth x Height)
Product weight	6.8 kg
Compatible Operating Systems	Mac OS X 10.9.5 or later, Windows 10 (32/64 bit), Windows 11, Windows 7 (32/64 bit), Windows 8 (32/64 bit), Windows 8.1 (32/64 bit), Windows Vista (32/64 bit), Windows XP Professional x64 Edition SP2 or later, Windows XP SP3 or later (32-bit), macOS 11 or later
Included Software	Epson Easy Photo Print, Epson Print CD, Epson Scan 2
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)
Mobile and Cloud printing services	Apple AirPrint, Mopria Print Service, Mopria Scan, Epson Smart Panel App, Epson Creative Print App, Epson Connect (Email Print, Scan-to-Cloud)
Colour	Black

OTHER FEATURES

Panel	Type: Color, Touchscreen, Diagonal:10.9 cm
-------	--

OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	C11CK46401
EAN code	8715946698793
Country of Origin	Indonesia



For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.
Last extracted: 2025-10-06

Expression Photo XP-8700

WHAT'S IN THE BOX

- Software (CD)
- Setup guide
- Power cable
- Main unit
- Individual Ink Cartridges
- Warranty document

INK CARTRIDGE COMPATIBILITY



INK YIELD DATA

	Squirrel 378	Squirrel 378XL
Black	240 pages*	500 pages*
Color (Cyan, Magenta, Yellow)	360 pages*	830 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

RECOMMENDED PAPER

<p>EPSON EXCEED YOUR VISION Photo Paper GLOSSY Papier Photo GLACE</p> <p>20 Sheets A4 82 x 117 210 x 297 mm 150 g/m²</p>	<p>Photo Paper Glossy</p> <p>200 g/m²</p>
<p>EPSON EXCEED YOUR VISION Value GLOSSY Photo Paper Papier photo GLACE économique</p> <p>20 Sheets 4" x 6" 102 x 152 mm 183 g/m²</p>	<p>Value Glossy Photo Paper</p> <p>183 g/m²</p>

1. see epson.co.uk/cartridgefootnotes