

12V DC 1A 12W UK Power Supply



TIGER PART: TP1004-ECO-L

Features:

- Supplied with fixed UK pins
- Universal 100-240vac input voltage
- Level VI efficiency
- Approved to latest EN62368-1 safety standard
- CE and UKCA approved
- Miniature Size
- Automatic Full safety protections including short circuit and over load
- Supplied by one of the UK's largest dedicated providers of power conversion products
- Fully automated production processed ensure low cost and high reliability



Part number:	TP1004-ECO-L-P25
Input voltage:	100-240vac (90-264vac max.)
Input frequency:	47 - 63Hz
Output voltage:	12 V DC
Current:	1000mA (1 amp)
Power :	12 Watts
Protection:	Short Circuit, Over Load
Dimensions:	67 x 47 x 74mm including pins & cable SR
Cord length:	1.5 metres
DC connector:	2.1 x 5.5 x 12mm 90 degree Right Angle
Polarity:	+ve centre (positive)
Leakage current:	<0.25mA
Operating temperature:	0°C to + 40°C

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.