

ADL20 4 to 20mA DC Current USB Datalogger

Built-in multifunction 2000 count LCD display

Features:

- Record up to 31,320 DC Current readings
- User adjustable sampling rate from 1 second to 24 hours
- High/Low Alarms with visual alert when settings are exceeded
- 2 LEDs indicate status of record and alarm
- USB interface for transferring recorded data to your PC
- Includes 3.6V Lithium battery, test leads with alligator clips, protective cap, and software

Applications:


Monitor single channel 4-20mA current loops commonly used in process control applications including temperature, pressure, flow, humidity, level, and other measurements

Eliminate manual recording of data over time



Specifications

Channels	Single, DC Current
DC Current Range	0 to 20.00mA
Accuracy	±0.5%
Resolution	0.01mA
Datalogger	31,320 points
Sample Rate	Selectable 1 second to 24 hours
PC Interface	USB port
Power	3.6V Lithium Battery (37-66)
Dimensions	4.2 x 0.9 x 0.9" (107 x 24 x 24mm)
Weight	2oz (55g)



Ordering Information:

ADL20 4 to 20mA DC Current USB Datalogger
37-66 3.6V Lithium Battery -2 pack

