

Technical data sheet

Article number:
157-00224

T50ROSFTOVAL12.5A

Product Group	1-piece fixing ties with fir tree, with disc, with stand-off, for oval holes
Product Family	with offset 12.5 and 25.0 mm
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	2.0 mm
CE Certification	No
Fixation Method	Fir Tree for oval holes
Flammability	UL 94 HB
for Hole Ø (FH)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Height (H)	13.15 mm
Length (L)	215.9 mm
Length (L2)	12.5 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C
Package Content	500 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 6.75 mm
Panel Thickness max.	6.75 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
Thickness (T)	1.35 mm
UV-Stabilised	Yes
Variant	Outside Serrated
Width (W)	4.70 mm

