

Technical Datasheet

Product Code: SSR6BKF**Description:** 250V 20A 6 Pole Female Screw Connector with Strain Relief

General Information

Rating	20A 250V~
Colour	Black
Materials	Body: Polyamide (PA6/6 V0) Contacts: Brass Silver Plated
Ingress Protection	IP20
Number Of Poles	6
Terminal Type	Screw (Cross Head)
Screw Torque	Terminals: 0.5Nm, Cover Screws: 0.6Nm
Terminal Cable Size	0.5mm ² Min. - 2.5mm ² Max.
Cut & Strip Lengths	Cut: Live & Neutral: 27mm, Earth: 33mm
Termination Lengths	Stripped: 7mm - 8.3mm
Temperature Rating	100°C
Dimensions	60mm (W) x 55mm (L) x 22mm (H)
Features	Installation couplers are only intended for connection and disconnection without load. This installation coupler is not suitable for installation in readily accessible areas.

