

MAQDC-830

PRODUCTS FOR INDUSTRIAL AUTOMATION

We recommend the following part:
Cordset: Single-Ended M12: BC-M12F8-24-10-SF



Cordset: Single-Ended M12
8-pin Straight Female
-10 m 8x24 Shielded Black PVC Jacket
Nickel-Plated Brass Coupling Nut
Part Number: 72510

CERTIFICATIONS



SPECIFICATIONS

IP Rating	IP67
Connector 1 Type	M12
Connector 2 Type	Flying Leads
Number of Ends	Single Ended
Connector 1 Number of Contacts	8
Coupling Nut Material	Nickel Plated Brass
Cable Jacket Material	PVC
Connector 1 Thread/Snap	Threaded
Cable Jacket Color	Black
Number of Conductors	8
Connector 1 Key Code	A
Wire AWG	24
Connector 1 Gender	Female
Outside Cable Diameter (mm)	5.59
Cordset Length (m)	10.0
Connector 1 Orientation	Straight
Overmold Material and Color	PUR Black
Shield/No Shield	Shield - Floating to Drain
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70
Current Rating (A)	2
Supply Voltage	30 V dc

Offline (Contact Us)

Item Status	RELEASED
Application	Signal
Connector 1 Body Size	Standard
Connector 1 Overmold Material and Color	PUR Black
Connector 1 Coupling Nut Material	Nickel Plated Brass
Connector 1 Shield	No Shield
Feature: Washdown Rated	No
Feature: Chemical Resistant	No
Oil/Grease Resistant	No