

75009605	DATA SHEET	
Valid from: 31.10.2018	EPIC® KIT H-A 3 BS AG	

Description

- H-A inserts, easy to service, with screw termination up to 2.5 mm² wire cross section
- The small H-A 3 is used whenever there is minimal space
- Easy cable connection with strait cable entry in the contacts.
- Optimally matched components
- Reduced ordering effort
- No wrong orders



Components of the combination

Article number of the combination	75009605
Housing	H-A 3 AG (10422000)
Insert	H-A 3 BS (10421000)

General characteristics

Series	H-A 3
Housing type	Socket housing
Version	Female
Connection type	Screw termination
Pin-arrangement	3 + PE
Contact diameter	1 mm
Termination cross section	Screw termination: 0,5 – 2,5 mm ² (2,5 mm ² with wire end sleeve, depending on crimp profile)
Degree of protection (DIN EN 60529)	IP 65 (latched)
Degree of protection (NEMA 250/UL 50E)	12, 4 (latched)
Cycles of mechanical operation	100
Temperature range	-40°C to +125°C, short term up to +125

Materials and surfaces

Housing, base material	PA, grey
Leaver	Zink plated steel
Sealing	NBR
Insert	PA
Contact, base material	Copper alloy
Contact, surface	Hard-silver

Electrical characteristics

Rated Voltage, IEC	400 V
Rated Voltage, UL	600 V
Rated Voltage, CSA	600 V
Rated Impulse Voltage	4 kV
Rated Current, IEC	23 A
Rated Current, UL	10 A
Rated Current, CSA	10 A
Contact Resistance	1,5 - 4 mOhm
Degree of Soiling	3

Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB75009605EN Version: 00	Page 1 of 3
---	---------------------------------------	-------------

75009605	DATA SHEET	
Valid from: 31.10.2018	EPIC® KIT H-A 3 BS AG	

Approvals

VDE-Approval, VDE-REG.-Nr.

B437

UL File Number

E75770

CSA File Number

053004




Standards

Safety Standard


IEC 61984; UL 1977; CSA-C22.2

Technical Drawings

Housing



Insert



Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB75009605EN Version: 00	Page 2 of 3
---	---------------------------------------	-------------

75009605	DATA SHEET	
Valid from: 31.10.2018	EPIC® KIT H-A 3 BS AG	



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Assembly time



Space requirement

Info

Compact, robust housings size H-A 3
Robust power supply connector
Straight cable entry into the contacts

Application range

Machine and equipment manufacturing
Control engineering
Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB75009605EN Version: 00	Page 3 of 3
---	---------------------------------------	-------------