

34G6QUK

Hisense

Monitor



AMD
FreeSync
Premium

General information

Model name:	34G6QUK	Series:	G6Q
Type:	LCD monitor	Material of frame:	Plastic
Colour of appliance:	Black	Cabinet material:	Plastic
Stand colour:	Black	Stand material:	Metal/Plastic

Panel performance

Panel aspect ratio:	21:09	Screen diagonal size (inch):	34 in
Resolution max.:	WQHD 3440x1440	Angle of visibility:	178 °
Wide colour gamut:	Yes	Frequency:	240 Hz
Contrast:	4000:1	Brightness:	300 nits
Brightness max.:	400 nits	Backlight technology:	ELED
Local dimming:	No	Local dimming zones:	No
3D technology:	No	2D to 3D:	No
HDR technology:	HDR400	HLG technology:	No
Dolby technology:	No	Quantum Dot Colour:	No

Improving engines

Upscaling Ultra HD:	No	Input lag in game mode:	No
3D digital comb filter:	No	MPEG noise reduction:	No
Mosquito noise reduction:	No		

Sound

Sound output power:	2x2 W	Sound technology:	No
User equalizer:	No	Dolby Atmos system:	No

Convenience

Media player:	No	User interface:	No
---------------	-----------	-----------------	-----------

Internet

Important apps:	No	Screen sharing:	No
Content sharing:	No	Airplay 2 support:	No

Reception and TV features

Digital and analog tuner:	No	Parental control:	No
PVR function:	No	Time shift:	No

Connectivity

Common interface (CI+):	No	HDMI1 connector:	HDMI2.0
HDMI2 connector:	HDMI2.0	HDMI3 connector:	No
HDMI4 connector:	No	Number of headphone outputs:	1
WiFi technology:	No	Bluetooth:	No
Light sensor:	No		

Eco and power supply

Voltage:	100-240 V	Energy efficiency class SDR:	F
Power consumption in working mode max.:	65 W		

Accessories

VESA Wall Mount Compatible:	75x75		
-----------------------------	--------------	--	--

Weight and dimensions

Product position at packing:	Vertical	Width of the packed product:	901 mm
Height of the packed product:	466 mm	Depth of the packed product:	205 mm
Width of the television with stand:	798 mm	Height of the television with stand:	526 mm
Depth of the television with stand:	298 mm	Width of the product:	798 mm
Height of the product:	363 mm	Depth of the product:	161 mm
Single stand:	Yes	Adjustable stand:	Yes
Distance between stands min.:	No	Cable management:	No
Product code:	20016855	EAN code:	6942351423111