



LG UHD AI 55UA73003 TV 139.7 cm (55") 4K Ultra HD Smart TV Wi-Fi Black

Brand : LG

Product family: UHD AI

Product code: 55UA73003

Product name : 55UA73003



LG UHD AI 55UA73003. Display diagonal: 139.7 cm (55"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LED, Screen shape: Flat, LED backlighting type: Direct-LED. Smart TV. Native aspect ratio: 16:9. Digital signal format system: DVB-C, DVB-S, DVB-S2, DVB-T, DVB-T2. Wi-Fi, Ethernet LAN. Product colour: Black



Display		Performance	
Display diagonal *	139.7 cm (55")	Smartphone/tablet remote support	✓
HD type *	4K Ultra HD	Ports & interfaces	
Display technology *	LED	PC in (D-Sub) *	✗
LED backlight	✓	Ethernet LAN (RJ-45) ports	1
LED backlighting type	Direct-LED	USB 2.0 ports quantity *	2
Screen shape *	Flat	Digital audio optical out	1
Native aspect ratio *	16:9	RF ports quantity	2
Native refresh rate	60 Hz	Common interface (CI) *	✓
Display resolution *	3840 x 2160 pixels	Common interface Plus (CI+) *	✓
Display diagonal (metric)	139 cm	HDMI ports quantity *	3
TV tuner		Consumer Electronics Control (CEC)	SimpLink
Tuner type *	Analog & digital	Power	
Digital signal format system *	DVB-C, DVB-S, DVB-S2, DVB-T, DVB-T2	Power consumption (standby) *	0.5 W
Smart TV		Energy efficiency class (SDR) *	F
Smart TV *	✓	Energy efficiency class (HDR) *	G
Internet TV *	✓	Energy consumption (SDR) per 1000 hours *	77 kWh
Operating system installed *	WebOS	Energy consumption (HDR) per 1000 hours *	105 kWh
Operating system version	25	AC input voltage	100 - 240 V
Apple AirPlay 2 support	✓	AC input frequency	50/60 Hz
Audio		Energy efficiency scale	A to G
Number of speakers *	2	Power supply type	Internal
RMS rated power *	20 W	Brand-specific features	
Sound modes	AI Sound Pro, Clear Voice Pro	AI Super Upscaling 4K, Bluetooth Surround Ready, Filmmaker Mode™, LG Sound Sync, ThinQ™, WOW Orchestra, Works With Apple HomeKit	
TV Sound Mode Share	✓	LG technologies (AV/TV)	
Enhanced Audio Return Channel (eARC)	✓	Weight & dimensions	
Network		Width (with stand)	1226 mm
Wi-Fi *	✓	Depth (with stand)	292 mm
Wi-Fi standards	Wi-Fi 5 (802.11ac)	Height (with stand)	776 mm
Bluetooth *	✓	Weight (with stand)	10.4 kg
Bluetooth version	5.1	Width (without stand)	1226 mm
Ethernet LAN *	✓		

Network		Weight & dimensions	
Web browser	✓	Depth (without stand)	58.9 mm
Design		Height (without stand)	710 mm
Product colour *	Black	Weight (without stand)	10.2 kg
VESA mounting *	✓	Stand width	122.3 cm
Panel mounting interface	300 x 300 mm	Stand depth	29.2 cm
Introduction year	2025	Packaging data	
Performance		Package width	1385 mm
High Dynamic Range (HDR) technology	Dynamic Tone Mapping, High Dynamic Range 10 Pro (HDR10 Pro), Hybrid Log-Gamma (HLG)	Package depth	128 mm
Audio formats supported	AAC, AC3, AC4, EAC3, HE-AAC, MP2, MP3, PCM, apt-X	Package height	830 mm
High Dynamic Range (HDR) supported *	✓	Package weight	14.9 kg
Game features	Auto Low Latency Mode (ALLM), Game Optimizer, HGiG, Variable Refresh Rate (VRR)	Package type	Box
Multi View	✓	Packaging content	
		Desktop stand	✓
		Remote control included	✓



8806096340264

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.