ACCLIMATE™

IP67 SEALED USB-C PANEL MOUNT




BCU/BPCU/BRU SERIES

BCU
Mates with:
BPCU, BRU

BPCU
Mates with:
BCU

BRU
Mates with:
BCU


BCU	–	END 1	–	PLATING OPTION	–	ASSEMBLED LENGTH	–	END 2 OPTION	–	STYLE
		–C = Sealed Type C Plug		**–S** = 30 µ" (0.76 µm) Gold		**–0.50** = .5 meter **–1.00** = 1 meter **–2.00** = 2 meters Standard Lengths		**–UC** = Unsealed Type C Plug **–SC** = Sealed Type C Plug **–BC** = Blunt Cut		**–P** = Plastic



SPECIFICATIONS


Overmold & Inner Mold:
PVC, Black (BCU)
Lock Nut:
Thermoplastic, Black (BCU)
Rubber Pad:
Silicone, Black (BCU)
Housing Material:
Thermoplastic, Black (BPCU, BRU)
Gasket Material:
Silicone, Black (BPCU, BRU)
Hex Nut:
Thermoplastic, Black (BPCU, BRU)
Operating Temp Range:
-40 °C to +85 °C

BPCU	–	END 1	–	PLATING OPTION	–	ASSEMBLED LENGTH	–	END 2 OPTION	–	STYLE
		–C = Sealed Type C Receptacle		**–S** = 30 µ" (0.76 µm) Gold		**–0.25** = .25 meter **–0.50** = .5 meter **–0.75** = .75 meter **–1.00** = 1 meter Standard Lengths		**–UC** = Unsealed Type C Plug **–BC** = Blunt Cut		**–P** = Plastic




DUST CAP
DCA-BRU-C-01

PANEL OPENING



BRU	–	C	–	PLATING OPTION	–	LEAD STYLE	–	STYLE
				–S = 30 µ" (0.76 µm) Gold		**–VT** =Vertical **–RA** = Right-angle		**–P** = Plastic



Note:
Some lengths, styles and options are non-standard, non-returnable

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.