

18W (1.5A max) Regulated Multi Voltage

UK Power Supply



Part number SW4177

- Regulated selectable DC output voltage
- Choice of 7 output voltages
- Choice of 6 Industry Standard DC connectors
- Reliable and Safety Approved
- 1.5 amp max. current (18W)



Input voltage	100 to 240V AC	
Input frequency	50 to 60Hz	
No load power consumption	0.3W	
Input full load current	0.25A	
Output voltage options	3V 1.5A (4.5W) / 4.5V 1.5A (6.75W) / 5V 1.5A (7.5W) / 6V 1.5A (9W) 7.5V 1.5A (11.25W), 9V 1.5A (13.5W), 12V 1.5A (18W)	
Max load output current	1.5 amp	
Noise test	20MHz.Each output bypassed by a 10uF 0.5% Input 90 to 264V AC output loaded at full load	
Input to output isolation	3000V AC 5mA 50/60Hz	
Input to case	3000V AC 5mA 50/60Hz	
Output to case	1500V AC 5mA 50/60Hz	
Isolation resistance	100MΩ	
Operating temperature	0°C to +25°C	6 DC Tips include
Storage temperature	-20°C to +50°C	2.1 x 5.5mm
Operating humidity	20%–85% RH. Non–condensing	2.5 x 5.5mm
Storage humidity	10%–90% RH Non–condensing	1.7 x 4.0mm
Dimension	76.5(L)x 42.4(W)x 72.2(H)mm	1.35 x 3.5mm
Weight	140g	1.1 x 3.0mm
		2.5 x 0.7mm

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.