

Empower your view with the Q27E4U 27" QHD monitor featuring 120Hz, height adjustability, and a 5-year warranty

Empower your view with the Q27E4U 27" QHD Monitor, delivering stunning 2560x1440 resolution and a smooth 120Hz refresh rate for seamless performance. Enjoy ergonomic comfort with its height-adjustable stand and protect your eyes with hardware-based anti-blue light technology. Built for reliability and long-term use, the Q27E4U comes with an impressive 5-year warranty, making it the perfect choice for work.



Features



QHD Resolution

With 2560 x 1440 resolution, Quad HD (QHD) offers superior picture quality and sharp imagery that reveals the finest details. The widescreen 16:9 aspect ratio provides plenty of space to spread out and work, plus allows you to enjoy games or movies in their original size.



120Hz Refresh Rate

Equip yourself with twice the frame rate of other monitors and say goodbye to image stuttering and blurry motion. With a 120Hz refresh rate every frame is rendered sharply and in smooth succession, so you can line up your shots accurately and appreciate high speed races in all their glory.



Height adjustable Stand

Raise or lower the screen to suit each individual's height and seating preferences. The easy-to-adjust stand ensures hours of comfort.



Anti-Blue light

AOC has created an innovative solution to protect against the damaging effects of blue light from computer screens. AOC's Anti-Blue Light technology is revolutionary in reducing the intensity and strength of blue light from computer screens while still maintaining true color and clarity.

GENERAL	
Model Name	Q27E4U
Brand	AOC
Channel	B2B
Product line	Essential-line
Design family	E4
EAN	4038986182812

DISPLAY INFORMATION	
Screen size (inch)	27.0
Screen size (cm)	68.6
Flat / Curved	Flat
Display hardness	3H
Panel treatment	Antiglare (AG)
Pixel Pitch (mm)	0.2331
Pixels per Inch	109.0
Panel resolution	2560x1440
Aspect ratio	16:9
Panel type	IPS
Backlight type	WLED
Max Refresh rate	120 Hz
Response time GtG	4 ms
Static contrast ratio	1500:1
Dynamic contrast ratio	50M:1
Viewing angle (CR10)	178/178
Display colours	16.7M (8bits)
Brightness in nits	350 cd/m²
Local Dimming Zones	Global Dimming

VIDEO FEATURES	
Sync technology (VRR)	Adaptive Sync
HDR (High Dynamic Range)	HDR Mode
Blue Light Technology	Anti Blue Light
Colour space (sRGB) CIE 1976 %	121.9
Colour space (Adobe RGB) CIE 1976 %	91.6
Flicker-Free	Flicker Free

CABINET INFORMATION	
Bezel Colour (front)	Black
Cabinet colour (backside)	Black
Cabinet finishing (backside)	Texture
Removable stand	Yes
Speaker power	2 W x 2
Built-in speakers fire direction	Down fire
Kensington Lock	Yes
Vesa wallmount	100x100

ERGONOMICS	
Tilt	-5/30
Height adjust (mm)	150mm
Swivel	175°±5
Pivot	-90°~90°

SUSTAINABILITY	
TCO Certified	Yes
Energy star	Energy star 8
EPEAT	Yes
ECMA Eco declaration	Yes
Product carbon footprint (PCF)	Yes
WEEE	Yes
REACH compliant	Yes
RoHs compliant	Yes
HF	Yes
PVC/BFR free housing	Yes
Mercury free	Yes
Recycable packaging material	100 % recycable
Low Halogen	Yes
Carton material	Paper

POWER CONSUMPTION	
Power supply	Internal
Power consumption on (Energystar test method) in watts	21.53
Power consumption on (typical) in watts	31.0
Power consumption standby in watts	0.3
Power consumption off in watts	0.3
Energy class	D

REGULATORY COMPLIANCE	
CB	Yes
CE	Yes
TUV-GS-Mark	Yes
TUV Ergo	Yes
EAC	Yes
FCC	Yes

CONNECTIVITY INFORMATION	
HDMI	2.1 TMDS
DisplayPort	DisplayPort 1.2 x 1
USB Hub	Yes
USB type downstream	4
USB fast charge port	Yes
Audio Output	1x Audio out
USB Type upstream	1 x USB3.2 type B Gen 1, 5 Gbit/s
USB generation	USB 3.2 (Gen 1) (4 USB downstream ports) 5Gbit

PRODUCT DIMENSIONS	
Product dimensions incl. base (WxHxD) mm	616 × 398.7~548.7× 222
Product dimensions excl. base (WxHxD) mm	616 × 361.5 × 50.5
Packaging dimensions (WxHxD) mm	730 x 480 x 139
Gross weight incl. package (in kg)	9.05
Net weight excl. package (in kg)	6.15
Product without stand (kg)	4.14

WHAT'S IN THE BOX	
HDMI cable	1.8
Displayport cable	1.8
Power Cable	Yes
Power cable C13	1.8

OTHER INFORMATION	
Warranty period	5 years
MTBF	70.000 hours (excluded backlight) + 30.000 hours (including backlight)

LEGAL DISCLAIMER

The monitor may appear different from the feature image. The products, accessories, cable(s) supplied with the product may vary in type, quantity, and/or specifications in line with country- or region-specific requirements. Specifications are subject to change without notice. The above functionality may vary depending on the user's actual usage conditions. This product is sold with a limited manufacturer's warranty. Please refer to the warranty terms for coverage details. All Rights reserved.