



Trimmer LXT®

DRT50RTJX2

18V • 6/8 mm

Light brushless manual trimmer with a wide range of accessories for carpentry

Handy trimmer for carpentry or hobbies. With the router trimmer, you can cut grooves or decorative trimmings in wood. Compatible with 6 and 8 mm collets, guide rule, dust extraction adapter and edge milling and router modules. Wide range of blades. Equipped with an LED light.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	10000 - 30000 min ⁻¹
Max. Collet Capacity	0 - 1-3/8 "
Plunge capacity	0 - 40 mm
Plunge capacity with trimmer base	0 - 40 mm
Plunge capacity with plunge base	0 - 35 mm
Collet Capacity	6 / 8 mm
Sound Power Level (L _{WA})	89 dB(A)
Sound Pressure Level (L _{pA})	81 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,8 - 2,1 kg
Product Dimensions (L x W x H):	134 x 89 x 226 mm



Standard accessories

153489-2 - Grip complete 125 mm | 195563-0 - Plunge base set | 122703-7 - Trimmer Guide Assembly | 122965-7 - Straight guide assembly | 194733-8 - Dust nozzle set Ø 32 / 37 mm | 195559-1 - Dust Nozzle | 195564-8 - Guide Holder Set | 198987-9 - Router Tilt Base | 821552-6 - Makpac case (4) | 450128-8 - Battery cover,

Standard machines

DC18RC - Battery Charger LXT®