



M-MA Type Metallic Cable Glands

Part No.	CPC Code	Thread Size	Cable Range	Thread OD	Thread Length	Spanner Size
			mm	L2 (mm)	L1 (mm)	C&F (mm)
CGMAM12	CB19787 / CB19793	M12*1.5	4-7	12	6	14
CGMAM16	CB19788 / CB19794	M16*1.5	5-8	16	7	18
CGMAM16L	CB26020 / CB26024	M16*1.5	6-10	16	8	20/18
CGMAM20	CB19789 / CB19795	M20*1.5	8-12	20	8	22
CGMAM25	CB19790 / CB19796	M25*1.5	11-14	25	9	27/24
CGMAM25L	CB26021 / CB26025	M25*1.5	13-18	25	7.5	30/27
CGMAM32	CB19791	M32*1.5	16-22	32	11	34
CGMAM32L	CB26022 / CB26026	M32*1.5	18-25	32	8	40/34
CGMAM40	CB19792	M40*1.5	23-28	40	12	45
CGMAM40L	CB26023 / CB26027	M40*1.5	22-32	40	12	50/45

Material: Part A/C/F: Nickle plate brass; Part B/E: NBR; Part D: Nylon PA66

Working temperature: -40 to 100 °C in static state, instantaneous heat resistance up to 120 °C,
-20 to 80 °C in dynamic state, instantaneous heat resistance up to 100 °C.

Characteristics: Ultra-strong stretching resistance, waterproof, dustproof, and high ability to resist salt, acid, alkali, alcohol, grease and general solvent.