

2m Panel Mount USB Cable A to A, M/F, USB-A Male to Female Extension Cable, USB 5Gbps Panel Mount Adapter Cable

Product ID: USBPNLAFAM2M



This panel mount USB-A to USB-A extension cable lets you reposition a USB 5Gbps (USB 3.0/3.2 Gen 1) port for easier access and cleaner system layouts. With a flexible TPE jacket and a screw-mounted female connector, it is designed for secure installation in panels, enclosures, and workstations.

The USB-A female panel-mount connector includes integrated mounting flanges with screws to keep the port firmly in place in vibration-prone or high-use environments. This provides a consistent and accessible connection point for peripherals without requiring access to the back of a system.

By relocating frequently used USB ports to a fixed panel, the Panel Mount USB Cable helps reduce repeated strain on host ports. This makes it well suited for public-facing systems such as kiosks or shared workstations, as well as meeting rooms where controlled USB access is required.

Certifications, Reports and Compatibility



Applications

Features

- **Add a Panel-Mounted USB 5Gbps Port**: Extend a USB 5Gbps connection by 2m (6.6ft) with a panel mount USB-A female port, enabling clean integration into faceplates, rackmount panels, and workstations for easy external access

- **Secure, Screw-Mounted Connector Design**: Female USB-A port features integrated mounting flanges with screws, ensuring a stable, fixed connection point in high-use or vibration-prone environments; Flexible TPE jacket withstands tight bends and is RoHS compliant
- **Maintain USB 5Gbps Performance**: Ensure full USB 5Gbps (USB 3.0/3.2) throughput and 15W charging to connected peripherals such as external storage, capture devices, cameras, and USB network adapters
- **Improve Access and Reduce Port Wear**: Relocate frequently used USB-A ports to a convenient panel location, minimizing strain on host device ports and simplifying port layouts; Ideal for public kiosks or meeting rooms with controlled USB access
- **The IT Pro's Choice**: Our USB extension cables are engineered to deliver consistent performance in professional environments and are tested for lasting reliability on critical components; Backed by free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive

Performance

Type and Rate	USB 3.0 (5Gbps)
---------------	-----------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB Type-A (9 pin, 5 Gbps)

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	10%-90% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/28 AWG
Cable Length	6.6 ft [2 m]
Cable OD	0.2 in [5.5 mm]

Product Length	79.2 in [2012.2 mm]
Product Width	1.5 in [38 mm]
Product Height	0.5 in [12.7 mm]
Weight of Product	3.2 oz [91.7 g]

Packaging Information

Package Length	4.3 in [11.0 cm]
Package Width	7.5 in [19.0 cm]
Package Height	0.9 in [2.3 cm]
Shipping (Package) Weight	4.3 oz [123.0 g]

What's in the Box

Included in Package	1 - 2m USB-A Panel Mount Cable - M/F
---------------------	--------------------------------------

****Product appearance and specifications are subject to change without notice.***