

1. Information about the goods and manufacturer

Name of Goods

19mm × 20m PVC Insulation Tape

Description of Goods

Electrical Tape

Details of the supplier of the safety data sheet

Premier Farnell
150 Armley Road
Leeds LS12 2QQ
Tel. : +44 (0) 870 129 8608

Emergency telephone number

+44 (0) 870 202530

2. Composition / information on ingredients

2.1. Product Composition: Pressure sensitive adhesive tape

Ingredient	C.A.S. No.	% by Wt
Vinyl Tape with Rubber-Based Adhesive	Mixture	100

3. Hazard identification

This product is exempt from hazard classification according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

4. First aid measures

Skin contact : No need for first aid is anticipated
Eye contact : No need for first aid is anticipated
Inhalation : No need for first aid is anticipated.
If Swallowed : No need for first aid is anticipated.

5. Firefighting measures

In case of fire: Use a carbon dioxide or dry chemical extinguisher to extinguish.

6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Not applicable.

6.2. Environmental precautions

Not applicable

6.3. Methods and material for containment and cleaning up

Not applicable

7. Handling and storage

7.1. Precautions for safe handling

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements

8. Exposure controls / personal protection

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions. No engineering controls or personal protective equipment (PPE) are necessary.

9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form	: Solid
Odor, Colour, Grade	: Black Coloured Tape
Odor threshold	: Not Applicable
PH	: Not Applicable
Melting point	: No Data Available
Boiling Point	: Not Applicable
Flash Point	: Not Applicable
Evaporation rate	: Not Applicable
Flammability (solid, gas)	: Not Classified
Flammable Limits (LEL)	: Not Applicable
Flammable Limits (UEL)	: Not Applicable
Vapor Pressure	: Not Applicable
Vapor Density	: Not Applicable
Specific Gravity	: ≥ 1.0 g/cm ³
Solubility In Water	: Not Applicable
Solubility-non-water	: Not Applicable
Partition coefficient: n-octanol/water	: Not Applicable
Autoignition temperature	: No Data Available
Decomposition temperature	: Not Applicable
Viscosity	: Not Applicable

10. Stability / reactivity

This material is considered to be non-reactive under normal use conditions.

11. Toxicological information

Inhalation	: No health effects are expected
Skin Contact	: No health effects are expected
Eye contact	: No health effects are expected
Ingestion	: No health effects are expected

Additional Information:

1. This product, when used under reasonable conditions and in accordance with the directions for use, should not present a health hazard.
2. However, use or processing of the product in a manner not in accordance with the product's directions for use may affect the performance of the product and may present potential health and safety hazards.

12. Ecological information

This article is expected to present a low environmental risk either because use and disposal are unlikely to result in a significant release of components to the environment or because those components that may be released are expected to have insignificant environmental impact.

13. Disposal considerations

Dispose of contents/container in accordance with the local/regional/national/international regulations.

14. Transport information

14.1. Packaged with paper box.

14.2. Not to mix with causticity or volatility things, not to stress, non tumble, non shatter, prevent rain and damp during transportation.

14.3. The carriage is plane, or use wood support.

15. Regulatory information

Meet RoHS requirement

16: Other information

No Information.

Part Number
PVC TAPE 1920R
PVC TAPE 1920BL

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.