



STANLEY® FATMAX™ Dual Adjust Water Pump Plier – 300mm



STANLEY® FATMAX™ Dual Adjust Water Pump Plier

- Dual adjustment jaw system enables easier and fine adjustment in tight spaces.
- Grips onto flat, round, hex and square work pieces.
- Secondary teeth hardening (53-63 HRC)
- Slimmer head profile ensuring maximum access into tight spaces.
- Ratcheting mechanism for precise and fine adjustments, as well as preventing unintentional shifting of the jaws.
- Anti-pinch to reduce blisters and discomfort.
- Tri-material grip providing an ergonomic, comfortable and secure grip.
- Button adjustment suitable for left and right-handed users.
- NF ISO 8976, ISO 8976, DIN ISO 8976, ASME B107.500

Width - 111 mm

Height - 350 mm

Depth - 26 mm

Maximum jaw opening – 75mm

Number of Pieces - 1

If your STANLEY product becomes defective due to faulty materials or workmanship within 12 months from the date of purchase, STANLEY guarantees to replace all defective parts free of charge or – at our discretion – replace the unit free of charge. See <https://www.2helpu.com/STANLEY> for more information.