



VIDA LITE 300W PSU PPFC 12CM FAN power supply unit 24-pin ATX ATX Black

Brand : VIDA

Product code: AA-300-YY

Product name : LITE 300W PSU PPFC 12CM FAN

VIDA LITE 300W PSU PPFC 12CM FAN

VIDA LITE 300W PSU PPFC 12CM FAN power supply unit 24-pin ATX ATX Black:

Introducing the Vida Lite 300W PSU (AA-300-YY) - where power meets price tag! This ATX dynamo delivers a dazzling 300 watts of electrifying performance, keeping your system fully charged and ready for action. With a fully wired design for a direct power connection and an ultra-quiet 120mm black fan, this powerhouse ensures a cool and quiet operation. Featuring connectors that spark convenience, including 20+4 pin and SATA, it's compatible with ATX 12V systems and guarantees a shockingly smooth performance. Don't miss out on the Lite side of power - it's your ticket to a jolt of energy without the shocking aftermath. Backed by a 1-year warranty, the Vida Lite 300W PSU is where power meets practicality in a positively electrifying package.



Power		Performance	
Total power *	300 W	ATX version	1.3
AC input voltage *	230 V	Design	
AC input frequency	50/60 Hz	Product colour	Black
Power Factor Correction (PFC) type	Passive	Cooling type	Active
Number of +12V rail(s)	1	Fan diameter	12 cm
Max output current (+3.3V)	10 A	Fan location	Top
Max output current (+12V)	20 A	Illumination	✗
Max output current (+5V)	12 A	On/off switch	✓
Max output current (-12V)	0.5 A	Certificates	
Max output current (+5Vsb)	2 A	Compliance certificates	UKCA, CE, RoHS
Ports & interfaces		Weight & dimensions	
Motherboard power connector *	24-pin ATX	Width	150 mm
Number of SATA power connectors	6	Depth	85 mm
Number of PATA power connectors	3	Height	140 mm
Floppy disk drive connector	✓	Weight	1.17 kg
PCI Express connector	✗	Packaging data	
Performance		Package width	195 mm
80 PLUS certification *	No	Package depth	92 mm
Removable filter	✗	Package height	160 mm
Power supply unit (PSU) form factor *	ATX	Package weight	1.4 kg
		Package type	Box
		Technical details	
		Dangerous goods	✗
		Logistics data	
		Country of origin	China



5056733100963

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity. Automated scraping, data mining, or harvesting for the purpose of training machine learning models, neural networks, or artificial intelligence systems is strictly prohibited without a commercial license.