

PHILIPS



CD Soundmachine

Multi-source CD player

CDs, FM radio, USB

Bluetooth® 6.0, audio-in

Built-in cassette player



TAZ2200

Plays tapes, and everything else too

Ready to embrace the tape revival? This portable boombox features an integrated cassette deck as well as a CD player. You also get clear FM radio, steady Bluetooth® streaming, USB playback and an audio-in port for other devices.

Portable multi-source CD player

- Portable boombox-style CD player
- Plays all CD formats: CDs, CD-R, CD-RW
- Digital FM radio with up to 20 presets
- Easy wireless streaming via Bluetooth®
- Tape deck on board

Easy to place. Plays what you love.

- Connect to other sources via USB port and audio-in
- Two 2.5" speaker drivers. 6 W max (3 W RMS)
- Stereo sound with Dynamic Bass Boost
- Built-in carrying handle. Operates via AC or batteries*
- Integrated sleep timer

Made with environmentally friendly materials

- GRS-certified recycled plastic. Responsible packaging
- Dimensions: 285 x 125 x 245 mm

Highlights

Portable CD player



Whether you're discovering the joy of physical CDs for the first time or all over again, this top-loading CD player is a great choice for casual listening. It can read any kind of CD format, and the carry handle makes it easy to move around. Simply plug into an AC socket or insert six batteries* (type R14 C) and take it outside.

Digital FM radio



When you want to embrace the music source that's been around longer than CDs, the FM digital tuner makes it easy to find radio programmes to love. You can set up to 20 presets for the stations you listen to frequently.

Bluetooth® 6.0



Want to use this CD player as a portable speaker? Bluetooth® connectivity lets you stream sounds directly to the player from a compatible smart device, and Dynamic Bass Boost will rock your favourite basslines.

Built-in cassette player

The front-loading cassette player adds another way to listen. Whether you've held onto your mix tapes over the years or you're listening to cassettes for the first time, slip in a tape, press play and let the music roll.

USB playback, audio-in

For complete flexibility, there's also a USB port that lets you plug in a flash drive to enjoy your digital music collection. Or use the audio-in port to connect a turntable and play some records.

Sleep timer

If you like to drift off to sleep with music, an audiobook or the radio playing in the background, you can set the sleep timer for 120, 90, 60, 30 or 15 minutes. The CD player will enter standby mode after that time has elapsed.

Recycled materials



We use post-consumer recycled plastics in our products, and our packaging is made from FSC-certified recycled cardboard with inserts printed on recycled paper.



Specifications

Sound

Output power (RMS): 3W
Sound Enhancement: Dynamic Bass Boost
Sound System: Stereo
Speaker diameter: 2.5"
Volume Control: up/down

Loudspeakers

Built-in speakers: 2

Connectivity

USB: Type-A (playback)
Bluetooth profiles: A2DP, AVRCP
Audio in (3.5 mm)
Bluetooth version: 6.0

Tuner/Reception/Transmission

Antenna: FM Antenna
Auto digital tuning
Tuner bands: FM mono, FM stereo
Station presets: 20
RDS: No
Antenna type: Telescopic

Convenience

Display Type: LCD
Backlight colour: White
Sleep timer

Power

Battery type: LR14
Battery voltage: 1.5 V
Mains power: 100 V - 240 V, 50/60 Hz
Standby power consumption: <0.8 W (clock display on)
Number of batteries: 6*
Power type: AC; batteries*

Accessories

Quick start guide
Power cord
Warranty: Warranty leaflet, Safety sheet

Design

Colour: Black

Dimensions

Packaging Depth: 159 mm
Product depth: 245 mm
Weight incl. Packaging: 2.2 kg
Packaging Height: 278 mm

Packaging Width: 370 mm
Product width: 285 mm
Product height: 125 mm
Product weight: 1.35 kg

Audio Playback

Cassette Deck Technology: Mechanical
Disc Playback Modes: Fast Forward/Backward, Next/Previous Track Search, Repeat/Shuffle/Program
Playback Media: CD, CD-R, CD-RW
Number of decks: 1
USB Direct Modes: Play/Pause, Previous/Next, Fast Backward/Fast Forward, Stop, Repeat, Shuffle, Program Play
Loader Type: Top
Programmable Tracks: 20
Bluetooth mode: Play/Pause, Previous/Next

Compatibility

Smartphone/tablet APP control: No

Sustainability

Plastic shell: contains 85% GRS-certified recycled post-consumer Acrylonitrile Butadiene Styrene (ABS) TE-00132492

