

PHILIPS

True wireless headphones

Smart charging case

Noise Cancelling

4 mic technology

Detailed, natural sound



TAT6000BK

Great sound, multitasking smart case

You'll flow through your day with these great-sounding true wireless earbuds and their smart charging case. Noise cancelling lets you listen free from distractions, while the case lets you take control without reaching for your phone.

True wireless earbuds. Natural sound, smart case.

- Smart charging case. Touch controls for music and more
- Noise cancelling for your sounds, your focus, your world
- 4 mic technology. Clearer calls, even in crowded places
- Great sound even at low volume with Dynamic Bass

Simply all you need

- Up to 28 hours of play time
- Stable Bluetooth® connection and multipoint connectivity
- Comfy, water-resistant, customisable
- IPX5 rating and three sizes of silicone ear tips

Seamlessly brilliant

- Quick charge for 15 minutes and get an extra 3 hours
- Philips Headphones app. Custom control
- Warm, detailed, natural. Philips sound signature
- Responsible design and packaging

Highlights

Smart charging case

You can use this case to take calls, control playback and noise cancelling, tweak bass and treble, or find a missing earbud. The 1.47" touchscreen also features a clock and a timer, plus a torch function that emits bright white light. A true multitasker, the case can even take photos by remotely triggering the camera on your connected device.

Noise Cancelling

Music, calls, podcasts, movies. When you want to focus, you can activate and control noise cancelling via the earbud's touch controls, the smart case or our companion app. Handy features include Awareness Mode to let outside sounds back in. Quick Awareness enhances voices so you can have a conversation without removing an earbud.

4 mic technology

If you're on a call, our four-mic setup and a noise-reduction algorithm will combine to pick up the sound of your voice and quieten background noise. Even if you're in a busy cafe, your voice will come through clearly and the person you're speaking to won't need to listen to all the other conversations going on around you as well!

Great sound. Dynamic Bass

You won't need to turn up the volume to get the best sound out of the 10 mm drivers in these true wireless earbuds. Activate Dynamic Bass via the customisable earbud controls or the Philips Headphones app and you can enjoy the full power of your favourite basslines even if listening quietly.

28 hrs of play time (7 + 21)

With noise cancelling off, you get 7 hours play time from a full charge and an extra 21 hours from the smart charging case (with noise cancelling on, you get 5 hours and an extra 16 from the case). For a quick boost, 15 minutes gives you an extra 3 hours. The case can be charged via USB-C.

Bluetooth® 5.4, multipoint

Bluetooth® 5.4 brings you a steadier connection for seamless streaming without annoying dips in the sound, even in built-up areas. Multipoint connectivity lets you connect to two Bluetooth® devices at the same time and you can easily manage connected devices via the Philips Headphones app.

Philips Headphones app

Our handy companion app makes it easy to adjust settings for the smart charging case, including how long the screen stays on and

whether it displays a 12- or 24-hour clock. You can also use the app to personalise noise cancelling, activate a low-lag setting for gaming, get the latest firmware and more.

Responsible design

We're continually working to make our supply chain more sustainable and transparent. These earbuds are made with RCS-certified, post-consumer recycled plastics and our plastic-free packaging uses FSC-certified recycled cardboard and soy-based ink.

IPX5 and comfy in-ear fit

An IPX5 rating means these buds can handle the moisture if you sweat and a little light rain won't bother them either. You get three sizes of silicone ear tips for the perfect fit and you can customise how the earbud touch controls are set up via the Philips Headphones companion app.

Philips sound signature

The custom drivers in these headphones are tuned to Philips sound signature, which brings you warm, detailed sound with rich bass. Whatever you're listening to, you'll love what you hear.

Specifications

Sound

Acoustic system: Closed
Frequency range: 20 - 20,000 Hz
Speaker diameter: 10 mm
Impedance: 16 Ohm
Maximum power input: 5 mW
Sensitivity: 105 dB (1 kHz)
Driver type: Dynamic

Connectivity

Bluetooth version: 5.4
Bluetooth profiles: A2DP, AVRCP, HFP
Maximum range: Up to 10 m
Multipoint connection
Supported codec: SBC

Outer Carton

Length: 23.00 cm
Number of consumer packages: 24
Width: 22.00 cm
Gross weight: 4.35 kg
Height: 30.60 cm
GTIN: 1 48 95229 16543 1
Net weight: 1.92 kg
Tare weight: 2.43 kg

Convenience

Automatic power off
Volume control
Water resistance: IPX5
Philips Headphones app support
Mono mode for TWS
Firmware updates possible
Type of controls: Touch

Inner Carton

Length: 10.80 cm
Number of consumer packages: 3
Width: 9.80 cm
Height: 13.50 cm
Net weight: 0.24 kg
Gross weight: 0.50 kg
Tare weight: 0.26 kg
GTIN: 2 48 95229 16543 8

Power

Number of batteries: 3 pcs
Music play time (ANC on): 5 + 16 hour(s)
Music play time (ANC off): 7 + 21 hour(s)
Fast charging time: 15 mins for 3 hrs

Battery type (Charging case): Lithium Polymer (built-in)
Battery type (Earbud): Lithium Polymer (built-in)
Battery weight (Total): 10.1 g
Battery capacity (Case): 410 mAh
Battery capacity (Earbud): 50 mAh

Packaging dimensions

Height: 11 cm
Packaging type: Carton
Type of shelf placement: Hanging
Width: 9.5 cm
Depth: 3.9 cm
Number of products included: 1
EAN: 48 95229 16543 4
Gross weight: 0.106 kg
Net weight: 0.080 kg
Tare weight: 0.026 kg

Accessories

Quick Start Guide
Eartips: 3 pairs (S/M/L)
Charging case
Charging cable: USB-C cable, 200 mm

Design

Colour: Black
Ear coupling material: Silicone
Ear fitting: In-ear
In-ear fitting type: Silicone ear-tip

Telecommunication

Microphone for call: 4 mics

Dimensions

Charging case dimension (W x D x H): 3.00 x 6.60 x 4.20 cm
Earbud dimension (W x D x H): 2.90 x 2.10 x 2.30 cm
Total weight: 0.056 kg

UPC

UPC: 8 40063 20663 2

ANC features

ANC technology: Hybrid
Awareness mode
Adaptive ANC
Microphone for ANC: 4 mic
ANC (Active Noise Cancelling)

Voice assistant

Voice assistant compatible: Apple Siri, Google Assistant
Voice assistant activation: Multi-Function touch
Voice assistant support

Sustainability

Plastic shell: contains 76% RCS certified recycled post-consumer Polycarbonate TE-00132492

