




ANSMANN Home Socket HS220

Compact 20 W socket adapter with additional USB-A & USB-C socket.

Features

- versatile socket adapter
- 250 V socket
- Integrated USB ports (USB-A and USB-C) with 20 W output
- Space-saving design
- Use at home, in the office or when travelling
- Robust construction and high-quality materials
- Long battery life



Article number: 1001-0184

Product content: Socket adapter, operating instructions



Specifications

Output voltage	5V DC			
Input voltage	100 - 240V AC			
Max. output current	3 A			
Charging currents	Mode	Voltage range	Max. current	Max. power
	USB A	5 V	3,0 A	15,0 W
	USB A	9 V	2,0 A	18,0 W
	USB A	12 V	1,5 A	18,0 W
	USB C	5 V	3,0 A	15,0 W
	USB C	9 V	2,2 A	20,0 W
	USB C	12 V	1,7 A	20,0 W
	PPS	3,3 - 5,9 V	3,0 A	17,7 W
	PPS 2	5 - 11 V	1,8 A	19,8 W
	USB A + USB C	5 V	3,0 A	15,0 W
	Steckdose	230 V AC	16,0 A	3680,0 W
USB-Ports	2			
Port	USB-A / USB type C			
Maximum power	20 W			
Average operational efficiency	82,7 %			
Efficiency at low load	82,2 %			
Power consumption at no load	0,100 W			
Charging protocol	Power Delivery Profile 3 / Power Delivery Profile 2 / PPS / Quick Charge 2.0 / Quick Charge 3.0 / Quick Charge 4.0			

Color	white
Operating temperature	0 - 25 °C
Storage temperature	-40 - 80 °C
Dimensions	79.5 × 72 × 46 mm