



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	5.30 - 6.20 mm
------------------------------------	----------------

Size	2B
------	----

Series	B - Indoor keyed
--------	------------------

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-762-dn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Shell style / Model id	FG - B series cable collet
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet
Keying	No keying
Weight	4.35 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Salt Spray Corrosion	>1000 hr

Cable fixation

Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.20 mm

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-762-dn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.