



PRODUCT CHANGE NOTIFICATION

GAS DISCHARGE TUBES



2035 Series Miniature 2-Pole Gas Discharge Tube

Change to Manufacturing Location, Design and Materials

Riverside, California – July 10, 2026 – As part of Bourns' strategic initiative to strengthen its global manufacturing footprint, production of 2035 Series Miniature 2-Pole Gas Discharge Tube Surge Protectors will transition to an expanded manufacturing location, effective January 4, 2027. This initiative reflects the consolidation of production within Bourns' existing manufacturing network, improving operational efficiency and reinforcing supply chain resilience to better serve our customers' evolving demand. A list of affected part numbers is included on page 2.

The country of origin for the 2035 Series Miniature 2-Pole Gas Discharge Tube will change from Costa Rica to China. The product incorporates a revised design and updated materials aligned with the capabilities and processes of the new manufacturing location. As a result, the form, fit and function will change. Established and standardized quality controls, lot traceability, and continuous monitoring processes across Bourns' manufacturing locations ensure that the quality and reliability of the affected parts will remain unchanged.

The form, fit, and function are changing because the 2035 Series Miniature 2-Pole Gas Discharge Tube will have updated electrical and mechanical specifications due to part changes associated with the location change. These updated specifications are provided in the Electrical and Mechanical Specifications Changes Table and Impulse Sparkover Specification Changes Table at the end of this document.

These changes have been validated through Bourns' qualification processes, in alignment with applicable industry standards and market requirements. Bourns recommends that customers test the affected part numbers in their specific applications to verify satisfactory performance.

There are no changes to the Bourns® part numbering scheme, branding, safety certification or applicable test methods (ITU-T K.12, IEEE C62.31, IEC 61643-311) for the part numbers listed below.

Parts manufactured prior to January 4, 2027, will reflect the current specifications, while the updated values will apply to all parts from that date forward.

Implementation dates are as follows:

Date that manufacturing of products at the current location will cease: **December 18, 2026**

Date that deliveries of products manufactured at the new site will begin: **January 4, 2027**

First date code using the above changes: **2701**

Bourns may fulfill orders for part numbers listed in the Affected Part Number table from either the current or the new manufacturing site until the existing supply from the current location is exhausted. During this transition period, shipments will reflect the specifications of the producing site, and customers can identify the source through the lot code and date code on each shipment.

Users should verify that the described changes will not impact the performance of the product in their specific applications.

GDT2615

Bourns will support customers throughout implementation of this transition. Product samples and technical documentation are available. Additional information can be obtained through Customer Service or Inside Sales.

Affected Part Numbers

2035-09-ALF	2035-20-ALF	2035-25-ALF	2035-35-ALF	2035-42-ALF	2035-60-ALF
2035-09-BLF	2035-20-BLF	2035-25-BLF	2035-35-BLF	2035-42-BLF	2035-60-BLF
2035-09-BT1LF	2035-20-BT1LF	2035-25-BT1LF	2035-35-BT1LF	2035-42-BT1LF	2035-60-BT1LF
2035-09-B5LF	2035-20-B5LF	2035-25-B5LF	2035-35-B5LF	2035-42-B5LF	2035-60-B5LF
2035-15-ALF	2035-23-ALF	2035-30-ALF	2035-40-ALF	2035-47-ALF	
2035-15-BLF	2035-23-BLF	2035-30-BLF	2035-40-BLF	2035-47-BLF	
2035-15-BT1LF	2035-23-BT1LF	2035-30-BT1LF	2035-40-BT1LF	2035-47-BT1LF	
2035-15-B5LF	2035-23-B5LF	2035-30-B5LF	2035-40-B5LF	2035-47-B5LF	

Electrical and Mechanical Specification Changes

Specification	Characteristic	Previous Specification	New Specification
Electrical	DC Sparkover @ 100 V/s	±15 % V	±20 % V
Electrical	Impulse Sparkover @ 1000 V/us	Typical	Maximum
Electrical	Impulse Sparkover @ 1000 V/us	Check comparative Impulse Table	Check comparative Impulse Table
Electrical	Impulse Sparkover @ 100 V/us	Check comparative Impulse Table	Check comparative Impulse Table
Electrical	Impulse Discharge Current 10/700 µs 500 Operations	100 A	No longer specified in the Data Sheet
Electrical	Arc Voltage 1 A	~ 10 V	~15 V
Electrical	DC Holdover Voltage 135 V 52 V (2035-09) 80 V (2035-15)	< 150 ms	< 150 ms 52 V (2035-90, 2035-150) 80 V (2035-230)
Electrical	IR	10 GΩ	1 GΩ
Mechanical	Length (mm)	4.2 ±0.3	4.2 ±0.2
Mechanical	Pin Diameter (mm)	0.8 ±0.05	0.8 ±0.08
Packaging	Reel Pitch (mm)	5	10
Packaging	2035-xx-A	Bag 250 Units Box 1000 units	PVC Tray 100 units Box 500 units
Packaging	2035-xx-B	Bag 100 Units Box 700 units	PVC Tray 100 units Box 500 units
Packaging	2035-xx-B5	Bag 250 Units Box 1000 units	PVC Tray 100 units Box 500 units
Visual Marking	Ink Color	White/Blue	White/Blue with Blue Shade Variation

Impulse Sparkover Specification Changes				
	Impulse Sparkover 100 V/μs		Impulse Sparkover 1000 V/μs	
Model No.	Previous (typical)	New (maximum)	Previous (typical)	New (maximum)
2035-09	350	600	525	700
2035-15	400	600	550	700
2035-20	425	600	575	700
2035-23	450	600	600	700
2035-25	475	600	625	700
2035-30	525	650	650	800
2035-35	600	750	750	900
2035-40	650	850	800	1000
2035-42	675	850	850	1000
2035-47	750	900	950	1100
2035-60	950	1100	1100	1200

If you have any questions or need additional information, please feel free to [contact Customer Service/Inside Sales](#).