

Sockets



MSEB 2610 F 2,8 Au

Product	MSEB 2610 F 2,8 Au
description	Miniature safety built-in socket, 2mm diameter, gold-plated brass. Flat push-on Connection 2.8x0.8mm complying with DIN 46244. For installation into switch- panels and equipment Chassis till 8mm wall thickness. Installation hole: 8mm diameter
operating instruction	BA254
article-no. / *colour	9754557xx ● 00 black ● 01 red ● 02 blue ● 03 yellow ● 04 green ● 05 brown ● 06 gray ● 07 white ● 09 violet ● 88 yellow/ green
drawing	
technical data	
connection	flat connector 2.8 x 0.8 mm
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current (consider derating curve)	10 A
material socket	brass, gold plated
housing material	PA
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-2
UL	cURus E537895

2 mm safety system

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges
stand : May 11, 2026 12:33 PM