



Plugs

ASS 4-2



Product	ASS 4-2
description	Touch-protected safety adapter with spring-loaded 4 mm safety plug and rigid 2 mm safety socket for connection of 2 mm safety plugs, 1000 V system, IEC61010.
operating instruction	BA466
article-no. / *colour	● 00 black ● 01 red
drawing	
	
technical data	
connection	unsprung socket 2 mm
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current (consider derating curve)	10 A
material socket	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-2

⁽¹⁾contact the manufacturer for applications at deviating temperature ranges
 stand : November 13, 2025 5:59 PM